



Technical Specs

Item	Electronic Ballast
Start Type	Programmed
Lamp Type	T5 Lamps
Ballast Family	Centium(TM)
Number of Lamps	4
Voltage	120/277
Light Output	Normal
Min. Starting Temp.	-20 Degrees F
Amps AC	2.00 to 0.86
Input Watts	234 to 240
Number of F50BX Lamps	3 or 4

Number of F54T5 Lamps	3 or 4
Number of F55BX Lamps	3 or 4
Wiring Type	Series
Ballast Factor	1
Power Factor	Greater Than 0.98
Total Harmonic Distortion	Less Than 10%
Length	16-5/8"
Width	4-13/16"
Height	1-19/64"
Dimension Reference	G13