

**Adjustable Premum Die-Cast Step Baffle ☆☆**

Accent lighting for horizontal or vertical surfaces or recessed downlighting for sloped ceilings. Fully adjustable 358° horizontally, 30° vertically. Lamp is recessed and shielded by die-cast baffle or aperture cone to reduce glare.



COMPACT FLUORESCENT		INCANDESCENT				<b>1027</b> Black Baffle <b>1027CL</b> Specular Clear Alzak® Cone <b>1027WH</b> White Baffle
NON-IC	IC/AIRSEAL®	NON-IC	IC	IC/AIRSEAL®		
		<b>1002</b> 75W PAR30S 75W PAR16 50W PAR20	<b>1002IC</b> 75W PAR30S 75W PAR16 50W PAR20	<b>1004ICX-CDN</b> 75W PAR30S 75W PAR16 50W PAR20		
		<b>REMODELER</b>				
		<b>1003RS-CDN</b> 75W PAR30S 75W PAR16 50W PAR20				
COMPACT FLUORESCENT		INCANDESCENT				<b>1127</b> Black Baffle <b>1127CL</b> Specular Clear Alzak® Cone <b>1127WH</b> White Baffle
NON-IC	IC/AIRSEAL®	NON-IC	IC	IC/AIRSEAL®		
		<b>1102</b> 150W BR40 150W PAR38				
		<b>REMODELER</b>				
		<b>1103RS-CDN</b> 150W BR40 150W PAR38				

PAR30S = Short neck lamp only