

Lexan® Dish ☆



Even illumination from durable Lexan® diffuser, supplied with gasket to keep out dirt and moisture. Easy twist-lock relamping. Aluminum reflector finished in white. Economical choice for low budget applications. Suitable for wet locations, showers and spas.

Note: For dimming options, please consult the corresponding product Spec Sheet on www.canlyte.com.

<p>1078 Opal Lexan® 1078-12 Opal Lexan® (Carton of 12)</p>	COMPACT FLUORESCENT		INCANDESCENT		
	NON-IC	IC/AIRSEAL®	NON-IC	IC	IC/AIRSEAL®
	1001F13N120 1001F13N347 1X13W QT*	1004ICF13N120 1004ICXF13N120 1X13W QT*	1002 60W A19*	1002IC 40W A19	1004ICX-CDN 40W A19
		REMODELER	REMODELER		
		1004ICRF13N120 1X13W QT*	1003RS-CDN 60W A19*		
<p>1178 Opal Lexan® 1178-12 Opal Lexan® (Carton of 12)</p>	COMPACT FLUORESCENT		INCANDESCENT		
	NON-IC	IC/AIRSEAL®	NON-IC	IC	IC/AIRSEAL®
	1101F13N120 1101F13N347 1X13W QT*	1104ICF13N120 1X13W QT*	1102 75W A19*	1102IC 40W A19	1104IC-CDN 1104ICX-CDN 40W A19
	1101F18N120 1101F18N347 1X18W QT	1104ICF18N120 1104ICXF18N120 1X18W QT	1104IC-CDN 40W A19		
	REMODELER	REMODELER	REMODELER		REMODELER
	1103RF18N120 1103RF18N347 1X18W QT	1104ICRF13N120 1X13W QT*	1103RS-CDN 75W A19*		1004ICRS-CDN 40W A19
		1104ICRF18N120 1X18W QT	1104ICRS-CDN 40W A19		

*See photometry p. 550 to 552.

Lytening Lexan® Dish ☆



Even illumination from durable Lexan diffuser. One trim size designed to be used with both 1004 and 1104 Lytening series frame-in kits. Easy twist-lock relamping. Suitable for wet locations, showers and spas.

Note: For dimming options, please consult the corresponding product Spec Sheet on www.canlyte.com.

<p>1178LX Opal Lexan®</p>	COMPACT FLUORESCENT		INCANDESCENT		
	NON-IC	IC/AIRSEAL®	NON-IC	IC	IC/AIRSEAL®
		1004ICF13N120 1X13W QT/TTT	1004IC-CDN 40W A19		1004IC-CDN 40W A19
		REMODELER	REMODELER		REMODELER
		1004ICRF13N120 1X13W QT/TTT	1004ICRS-CDN 40W A19		1004ICRS-CDN 40W A19
<p>1178LX Opal Lexan®</p>	COMPACT FLUORESCENT		INCANDESCENT		
	NON-IC	IC/AIRSEAL®	NON-IC	IC	IC/AIRSEAL®
		1104ICF13N120 1X13W QT/TTT	1104IC-CDN 52W A19		1104IC-CDN 40W A19
		REMODELER	REMODELER		REMODELER
		1104ICRF13N120 1X13W QT/TTT	1104ICRS-CDN 52W A19		1104ICRS-CDN 40W A19