

Premium Die-Cast Step Baffle Sloped Ceiling ☆☆

Each downlight features a 6-3/4" round opening that precisely matches other 6-3/4" downlights in shape and finish.

Shallow slope: Lower brightness downlighting for shallow sloped ceilings. 14°- 30° (3/12-7/12) Pitch.

Steep slope: Provides well-shielded downlighting for steep sloped ceilings. 30°- 45° (7/12-12/12) Pitch.



COMPACT FLUORESCENT		INCANDESCENT				SHALLOW SLOPE 1131BK Black Baffle 1131WH White Baffle
NON-IC	IC/AIRSEAL®	NON-IC	IC	IC/AIRSEAL®		
			1102IC 75W PAR30 (short or long neck) 75W BR30	1104ICX-CDN 75W PAR30 (short or long neck) 75W BR30		STEEP SLOPE 1133BK Black Baffle 1133WH White Baffle
COMPACT FLUORESCENT		INCANDESCENT				
NON-IC	IC/AIRSEAL®	NON-IC	IC	IC/AIRSEAL®		
			1102IC 75W PAR30S (short neck only) 75W BR30	1104ICX-CDN 75W PAR30S (short neck only) 75W BR30		