



Frost / Clear

100W 130V A19 FR 20W

The Philips Family of Standard Frost and Clear bulbs are good for everyday use. Clear bulbs provide sparkle, especially in fixtures that are made of chrome, have mirrored surfaces, multiple sockets or have cut glass parts. If glare is a problem, use a dimmer or a lower wattage bulb to reduce brightness. Clear bulbs are also used in fixtures with reflectors. Frost bulbs provide soft light with reduced glare.

Product data

• General Characteristics

Base	Medium [Single Contact Medium Screw]
Base Information	Aluminum [Aluminum Base]
Bulb	A19
Bulb Finish	Frosted
Filament Shape	C-9 [Pendant]
Operating Position	Universal [Any or Universal (U)]
Main Application	General Lighting
Atmosphere	Gas

• Electrical Characteristics

Energy Used	100 W
Voltage	130 V

• Product Dimensions


Light Center Length L	2.992 in
--------------------------	----------

Max. Overall Length (MOL) - C	4.438 (max) in
Diameter D	2.375 in

• Product Data

Order code	925283534304
Full product code	925283534304
Full product name	100W 130V A19 FR 20W
Order product name	100W 130V A19 FR 20W
Pieces per pack	2
Packs per outerbox	12
Bar code on pack - EAN1	046677286903
Bar code on outerbox - EAN3	50046677286908
Logistic code(s) - 12NC	925283534304

Dimensional drawing



Product	C (Max)	D (Norm)
Std 100W E26 130V A19 FR	4.438	2.375

PHILIPS

sense and simplicity

Dimensional drawing



© 2011 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2011, July 25
data subject to change