

INCANDESCENT LAMPS

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.‡	Description	Class Filament	LCL (In.)	MOL (In.)	Rated Avg. Life (Hrs.)(93)	Approx. MBCP*	Lumens
-------	------	------	----------------	--------------------	---------------	-------	------------	-------------	----------------	-----------	-----------	----------------------------	---------------	--------

INCANDESCENT LAMPS (BY WATTAGE) CONTINUED

300	PS35	Mog.	14320-6		300/RSIF	120	24	Frost Rough Service	C, C-9		9%	1000		5150
			14309-9		300/99IF	120–130	24	Frost Extended Service Ratings @120V=265W	C, C-9		9%	1000		4500
												2830		3420
			14321-4		300/99	120–130	24	Clear Extended Service Ratings @120V=265W	C, C-9		9%	2500		4600
												7134		3495
			14316-4		300/IF	120–130	12	Frost Ratings @120V=265W	C, C-9		9%	1000		4,600
												2854		3495
300	R40	Med.	14314-9		300	120–130	24	Clear Ratings @120V=265W	C, C-9	7	9%	1000		4600
												2854		3495
			14317-2		300	277	24	Clear	C, C-9	7	9%	1000		4000
			20474-3		300/IF/TG	120–130	12	TuffGuard Coated Lamp	C, C-9		9%	1000		
			14432-9	■▲	300R/FL/1	12	24	Reflector Flood Frost—Swimming Pool	C, C-2V		6%	2000		2960
			14429-5	■▲	300R/FL/1	120–130	24	Reflector Flood—Swimming Pool	C, CC-11		6%	2000		2480
300	R40	Mog.	14433-7	▲	300R/3FL	120–130	24	Reflector Flood	CC-11		7%	2000		3600
375	BR40	Med. Skt.	14342-0	(19,31,37,87)	375BR40	120	24	Reflector Infrared Lt. Frost Industrial	C, C-7A		7%	5000		
	R40	Med. Skt.	14574-8	(19,31,37,87)	375R40/1	120	24	Clear Reflector Infrared Industrial	C, C-7A		7%	5000		

For the most current product information, go to the e-catalog on www.philips.com
Incandescent symbols and footnotes located on page 149



PS35
Mog.



R40
Med.



R40
Mog.



BR40
Med. Skt.



R40
Med. Skt.