



PAR16

60PAR16/HAL/FL27 120V 15PK

Philips Halogen PAR lamps will provide bright, white light across the product line and feature excellent beam qualities for accent or ambient lighting. Their optimized coil and burner design allows for clear, crisp lighting effects with excellent color rendering, making it easy to optimize the look and feel of your store and your merchandise.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Bulb Shape	PAR16 [PAR 2 inch]
Operating Position	Universal [Universal]
Main Application	Indoor Reflector
Gas Filling	GAS
Life With 3 Hour Per Day Use	2.7 a

Light Technical	
Beam Angle (Nom)	27 °
Initial lumen (Nom)	580 lm
Luminous Intensity (Nom)	1800 cd
Beam Description	Flood [Flood]
Correlated Color Temperature (Nom)	2900 K
Color Rendering Index (Nom)	100

Operating and Electrical	
Power (Rated) (Nom)	60 W
Voltage (Nom)	120 V


Mechanical and Housing	
Bulb Finish	Clear (CL)
Cap-Base Information	Brass [Brass Cap]
Bulb Material	Hard Glass
Reflector Finish	Aluminized
Filament Shape	CC-8 [Axial]

Approval and Application	
Estimated Energy Cost Per Year	7.23 \$

Product Data	
Order product name	60PAR16/HAL/FL27 120V 15PK
EAN/UPC - Product	046677330064
Order code	330068
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	15
Material Nr. (12NC)	924757103607
Net Weight (Piece)	0.082 kg

PAR16

Dimensional drawing



Product

60PAR16/HAL/FL27 120V 15PK

HAL PAR16 60W E26/Brass 120V FL 27D

