

Product Number	Ordering Code	Watts	Volts	Pkg Qty.	Description	Bulb Type	Base	Rated Avg. Life (Hrs.) ¹	Approx. MBCP ²	Lumens	Class, Filament	MOL (In.)
Halogen PAR38³⁴												
22946-8	45PAR38/HAL/SP10	45	120	12	Spot 10°	PAR-38	Medium Skirted	3000	6200	530	C, CC-8	5%
22948-4	45PAR38/HAL/FL25	45	120	12	Flood 25°	PAR-38	Medium Skirted	3000	2000	530	C, CC-8	5%
14482-4	60PAR38/HAL/SP10	60	120	12	Spot 10°	PAR-38	Medium Skirted	3000	10,500	800	C, CC-8	5%
14483-2	60PAR38/HAL/FL25	60	120	12	Flood 25°	PAR-38	Medium Skirted	3000	3200	800	C, CC-8	5%
14484-0	60PAR38/HAL/WFL40	60	120	12	W.Flood 40°	PAR-38	Medium Skirted	3000	1300	800	C, CC-8	5%
14485-7	75PAR38/HAL/SP10	75	120	12	Spot 10°	PAR-38	Medium Skirted	3000	13,000	1050	C, CC-8	5%
14486-5	75PAR38/HAL/FL25	75	120	12	Flood 25°	PAR-38	Medium Skirted	3000	3800	1050	C, CC-8	5%
23069-8	90PAR38/HAL/SP10	90	120	12	Spot 10°	PAR-38	Medium Skirted	3000	16,400	1350	C, CC-8	5%
23070-6	90PAR38/HAL/FL25	90	120	12	Flood 25°	PAR-38	Medium Skirted	3000	5350	1350	C, CC-8	5%
14487-3	90PAR38/HAL/WFL40	90	120	12	W.Flood 40°	PAR-38	Medium Skirted	3000	2200	1350	C, CC-8	5%
22947-6	45PAR38/HAL/SP10	45	130	12	Spot 10° Ratings @ 120V = 40W	PAR-38	Medium Skirted	2500 5000	6200 4960	560 410	C, CC-8	5%
22949-2	45PAR38/HAL/FL25	45	130	12	Flood 25° Ratings @ 120V = 40W	PAR-38	Medium Skirted	2500 5000	2000 1600	560 410	C, CC-8	5%
14488-1	60PAR38/HAL/SP10	60	130	12	Spot 10° Ratings @ 120V = 53W	PAR-38	Medium Skirted	3000 6000	10,500 8400	800 610	C, CC-8	5%
14490-7	60PAR38/HAL/FL25	60	130	12	Flood 25° Ratings @ 120V = 53W	PAR-38	Medium Skirted	3000 6000	3200 2560	800 610	C, CC-8	5%
14491-5	60PAR38/HAL/WFL40	60	130	12	W.Flood 40° Ratings @ 120V = 53W	PAR-38	Medium Skirted	3000 6000	1300 1040	800 610	C, CC-8	5%
14492-3	75PAR38/HAL/NSP8	75	130	12	N. Spot 8° Ratings @ 120V = 66W	PAR-38	Medium Skirted	2500 5000	16,750 13,400	1100 840	C, CC-8	5%
14493-1	75PAR38/HAL/SP10	75	130	12	Spot 10° Ratings @ 120V = 66W	PAR-38	Medium Skirted	2500 5000	14,000 11,200	1100 840	C, CC-8	5%
14494-9	75PAR38/HAL/FL25	75	130	12	Flood 25° Ratings @ 120V = 66W	PAR-38	Medium Skirted	2500 5000	4350 3480	1100 1020	C, CC-8	5%
23650-5	90PAR38/HAL/SP10	90	130	12	Spot 10° Ratings @ 120V = 79W	PAR-38	Medium Skirted	2500 5000	16,400 13,120	1350 1020	C, CC-8	5%
23651-3	90PAR38/HAL/FL25	90	130	12	Flood 25° Ratings @ 120V = 79W	PAR-38	Medium Skirted	2500 5000	5350 4280	1350 1020	C, CC-8	5%
14495-5	90PAR38/HAL/WFL40	90	130	12	W.Flood 40° Ratings @ 120V = 79W	PAR-38	Medium Skirted	2500 5000	2200 1760	1350 1020	C, CC-8	5%

Shipping Data (Subject to change without notice)

Product Number	SKU UPC (0 46677-)	Outer Bar Code (5 00 46677-)	Case Qty.	Case Weight (lbs.)	Case Cube (cu. ft.)	Pallet Qty.	SKUs Per Layer	Layers High	SKU Dimensions (W x D x H) (In.)	Case Dimensions (W x D x H) (In.)	Pallet Dimensions (W X D X H) (In.)
Halogen PAR16											
26335-0	26335 5	26335 0	15	4.0	0.160	2160	360	6	2.1 x 2.1 x 3.3	7 x 11 x 4	39.36 x 42.76 x 23.28
26345-9	26345 4	26345 9	15	4.0	0.153	2160	360	6	2.1 x 2.1 x 3.3	7 x 11 x 4	39.36 x 42.76 x 23.28
33004-3	33004 0	33004 5	15	4.0	0.178	2160	360	6	2.1 x 2.1 x 3.3	7 x 11 x 4	39.36 x 42.76 x 23.28
33006-8	33006 4	33006 9	15	4.0	0.178	2160	360	6	2.1 x 2.1 x 3.3	7 x 11 x 4	39.36 x 42.76 x 23.28
26338-4	26338 6	26338 1	15	4.0	0.153	2160	360	6	2.1 x 2.1 x 3.3	7 x 11 x 4	39.36 x 42.76 x 23.28
26348-3	26348 5	26348 0	15	4.0	0.153	2160	360	6	2.1 x 2.1 x 3.3	7 x 11 x 4	39.36 x 42.76 x 23.28
33005-0	33005 7	33005 2	15	4.0	0.178	2160	360	6	2.1 x 2.1 x 3.3	7 x 11 x 4	39.36 x 42.76 x 23.28
33007-6	33007 1	33007 6	15	4.0	0.178	2160	360	6	2.1 x 2.1 x 3.3	7 x 11 x 4	39.36 x 42.76 x 23.28
Halogen PAR20											
22906-2	22906 1	22906 6	15	4.0	0.241	2970	270	11	2.44 x 2.44 x 3.5	7.81 x 12.81 x 4.25	38.44 x 46.86 x 46.75
22911-2	22911 5	22911 0	15	4.0	0.241	2970	270	11	2.44 x 2.44 x 3.5	7.81 x 12.81 x 4.25	38.44 x 46.86 x 46.75
13846-1	13846 2	13846 7	15	4.0	0.250	2970	270	11	2.44 x 2.44 x 3.5	7.81 x 12.81 x 4.25	38.44 x 46.86 x 46.75
22921-1	22921 4	22921 9	15	4.0	0.241	2970	270	11	2.44 x 2.44 x 3.5	7.81 x 12.81 x 4.25	38.44 x 46.86 x 46.75
Halogen PAR30 Long Neck											
22922-9	22922 1	22922 6	15	8.0	0.688	1215	135	9	3.5 x 3.5 x 4.75	10.94 x 18.06 x 5.5	39.94 x 47.06 x 49.50
22923-7	22923 8	22923 3	15	8.0	0.688	1215	135	9	3.5 x 3.5 x 4.75	10.94 x 18.06 x 5.5	39.94 x 47.06 x 49.50
22925-2	22925 2	22925 7	15	8.0	0.688	1215	135	9	3.5 x 3.5 x 4.75	10.94 x 18.06 x 5.5	39.94 x 47.06 x 49.50
22927-8	22927 6	22927 1	15	8.0	0.688	1215	135	9	3.5 x 3.5 x 4.75	10.94 x 18.06 x 5.5	39.94 x 47.06 x 49.50
22930-2	22930 6	22930 1	15	8.0	0.688	1215	135	9	3.5 x 3.5 x 4.75	10.94 x 18.06 x 5.5	39.94 x 47.06 x 49.50
22934-4	22934 4	22934 9	15	8.0	0.688	1215	135	9	3.5 x 3.5 x 4.75	10.94 x 18.06 x 5.5	39.94 x 47.06 x 49.50
22941-9	22941 2	22941 7	15	8.0	0.688	1215	135	9	3.5 x 3.5 x 4.75	10.94 x 18.06 x 5.5	39.94 x 47.06 x 49.50
22944-3	22944 3	22944 8	15	8.0	0.688	1215	135	9	3.5 x 3.5 x 4.75	10.94 x 18.06 x 5.5	39.94 x 47.06 x 49.50
13847-9	13847 9	13847 4	15	8.0	0.630	1215	135	9	3.5 x 3.5 x 4.75	10.94 x 18.06 x 5.5	39.94 x 47.06 x 49.50
22926-0	22926 9	22926 4	15	8.0	0.688	1215	135	9	3.5 x 3.5 x 4.75	10.94 x 18.06 x 5.5	39.94 x 47.06 x 49.50
22928-6	22928 3	22928 8	15	8.0	0.688	1215	135	9	3.5 x 3.5 x 4.75	10.94 x 18.06 x 5.5	39.94 x 47.06 x 49.50
13848-7	13848 6	13848 1	15	8.0	0.630	1215	135	9	3.5 x 3.5 x 4.75	10.94 x 18.06 x 5.5	39.94 x 47.06 x 49.50
22943-5	22943 6	22943 1	15	8.0	0.688	1215	135	9	3.5 x 3.5 x 4.75	10.94 x 18.06 x 5.5	39.94 x 47.06 x 49.50
22945-0	22945 0	22945 5	15	8.0	0.688	1215	135	9	3.5 x 3.5 x 4.75	10.94 x 18.06 x 5.5	39.94 x 47.06 x 49.50

- Rated average life is the length of operation (in hours) at which point an average of 50% of the lamps will still be operational and 50% will not.
 - For indoor or outdoor use. A weather-protected fixture is recommended for wet locations.
- Maximum Beam Candlepower
 - Suitable for use in open fixtures.
- To avoid deterioration of lampholder by heat, use only heat resistant lampholders or fixtures listed by a nationally recognized electrical testing organization for use with reflector or PAR lamps.
 - Do not exceed the maximum wattage rating of the fixture.
 - Do not use if outer glass is scratched or broken since it may break during operation or removal.
- PAR HALOGEN CAUTION NOTICE:** Before using bulb, see operating instructions on inside flap. Adherence to the operating instructions will reduce the risk of personal injury or fire. The filament capsule contained inside this glass bulb is pressurized, operates at high temperature and could unexpectedly shatter. Should the outer bulb break, particles of extremely hot glass could be discharged into the fixture and/or the surrounding environment, thereby creating a risk of personal injury or fire. Operating Instructions: Before replacing, turn off power and let lamp cool to avoid electrical shock or burn.
 - If outer glass breaks the lamp may continue to light, however; immediately discontinue use.
 - Due to the heat that radiates from the bulb, do not use in close proximity to combustible materials or objects susceptible to drying or fading.
 - Manage in accord with disposal laws.