



# EnduraLED 8W 2700K A19 Dimmable

## Product family description

Philips EnduraLED A-shape Dimmable LED lamp is the smart LED alternative to standard incandescents. They provide smooth dimming with less energy. Their long life properties eliminate the hassle of repeated relamping in busy areas.

## Features

- Smooth dimming to 10% of full light levels\*
- Designed for "Leading Edge" TRIAC dimming systems
- Instant-on light
- Emits virtually no UV/IR light in the beam.
- 25,000 hours rated average life+
- Contains no mercury.
- +Rated average life based on engineering testing and probability analysis.

## Benefits

- Offers diffuse light source when accenting a wide area
- Will not fade colors, avoids inventory spoilage
- 3-year limited warranty
- The 800 Series EnduraLED A-shape is designed to replace a standard 60W incandescent A19 lamp with 800 lumens.
- .

## Application

- Ideal for ambient lighting in hospitality, residential and government buildings.

Product data	
ProNumUS	409938
Full product name	EnduraLED 8W 2700K A19 Dimmable
OrdCodUS	409938
Pack type	
Pieces per Sku	1
Skus/Case	6
EANIUS	

# PHILIPS

Product data	
EAN2US	
EAN3US	
Successor Product number	
Additional Information	Dimmable
Cap-Base	E26
Bulb	A19
Wattage	8W
Dimmable	Yes
Color Code	WW
Color Designation (text)	Warm White
Correlated Color Temperature	2700 K
Luminous Flux	450 Lm
Color rendering index	80
Color Temperature	2700K [CCT 2700K]



**EnduraLED 8W E26 A19**



©2009 Koninklijke Philips Electronics N.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Document order number : 0000 000 00000