

## R40 23W ICT


## Product family description

Product data			
Product Number	157024		
Full product name	R40 23W ICT		
Ordering Code	157024		
Pack type	I Lamp in a Folding Carton		
Pieces per Sku	1		
Skus/Case	6		
Pack UPC	046677157029		
EAN2US			
Case Bar Code	50046677157024		
Successor Product number			
Base	Medium [Single Contact Medium Screw]		
Packing Type	ICT [I Lamp in a Folding Carton]		
Packing Configuration	6		
Ordering Code	EL/A R40 23W REFLECTOR		
Pack UPC	046677157029		
Case Bar Code	50046677157024		
Watts	23W		
Voltage	110-127V		
Line Frequency	50/60Hz		
Beam Angle	120D		
Approx. MBCP	350 cd		
Color Code	827 [CCT of 2700K]		
Color Rendering Index	82 Ra8		
Color Designation	Warm White		
Color Description	827 Warm White		
Color Temperature	2700 K		
Initial Lumens	1300 Lm		
Overall Length C	162 mm		
Diameter D	122 mm		
Product Number	157024		





## Cap-Base E26



Reflector

	С	D	F
Full product name	Max	Max	Max
R40 23W ICT	162	122	59.5



## ©2009 Koninklijke Philips Electronics N.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liablity will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights. Document order number : 0000 000 00000