



Sustainability policy at Philips Lighting:

Philips Lighting is committed to providing lighting solutions that improve people's lives and are environmentally sound. This philosophy is a cornerstone of our sustainability policy, which balances social, environmental and economic action.

COMPACT FLUORESCENT LAMPS

Energy Saver GU24, Genie, Soft White and Reflectors

Watts	Inc. Equiv. Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Pkg. Type	Case Qty.	MOL (In.)	Rated Avg. Life (Hrs.) (230)	Approx. Initial Lumens (231)	CRI
ENERGY SAVER UNIVERSAL GENIE												
14	60	SLS Genie	Med.	21053-4	\$ T †	14W Genie Pro Pack 6PK	Box	4	5 1/4	8000	800	82
18	75	SLS Genie	Med.	21055-9	\$ †	18W Genie Pro Pack 6PK	Box	4	5 1/4	8000	1100	82
ENERGY SAVER GU24 BASE TWISTER *AVAILABLE AUGUST 2008												
13	60	GU24 Twist	GU24	22285-1	\$ †	EL/mdT 13W GU24	Box	6	3 3/8	10,000	900	82
18	75	GU24 Twist	GU24	22286-9	\$ †	EL/mdT 18W GU24	Box	6	3 3/8	10,000	1200	82
23	100	GU24 Twist	GU24	22287-7	\$ †	EL/mdT 23W GU24	Box	6	4 1/8	10,000	1600	82
ENERGY SAVER SOFT WHITE PLUS												
9	40	SWP	Med.	15699-1	\$ ■ †	EL/A SWP 9W	Box	6	4 1/4	8000	450	82
				21207-6	\$ ■ †	BC-EL/A SWP 9W	Blister	4	4 1/4	8000	450	82
14	60	SWP	Med.	15700-8	\$ ■ †	EL/A SWP 14W	Box	6	4 3/8	8000	800	82
				21208-4	\$ ■ †	BC-EL/A SWP 14W	Blister	4	4 3/8	8000	800	82
				21209-2	\$ ■ †	BC-EL/A SWP 14W 3PK	Blister	4	4 3/8	8000	800	82
				21214-2	\$ †	BC-EL/A SWP 14W Bug-A-Way®	Blister	4	4 3/8	8000	600	N/A
				20371-1	\$ †	EL/A SWP 14W Bug-A-Way	Box	6	4 3/8	8000	600	N/A
20	75	SWP	Med.	20080-8	\$ T †	EL/A SWP 20W	Box	6	5 1/2	8000	1100	82
ENERGY SAVER REFLECTOR FLOOD												
14	50	R20	Med.	15701-6	\$ ■ †	EL/A R20 14W	Box	6	4 3/8	8000	500	82
				21215-9	\$ ■ †	BC-EL/A R20 14W	Blister	3	4 3/8	8000	500	82
				21219-1	\$ ■ †	BC-EL/A R20 14W 2PK	Blister	3	4 3/8	8000	500	82
15	75	R30	Med.	15703-2	\$ ■ †	EL/A R30 15W	Box	6	5 1/4	8000	750	82
16	75	R30	Med.	21220-9	\$ ■	BC-EL/A R30 16W	Blister	2	5 1/8	8000	750	82
				15279-3	\$ ■	BC-EL/A R30 16W 2PK	Blister	2	5 1/8	8000	750	82
23	120	R40	Med.	15702-4	\$ ■ †	EL/A R40 23W	Box	6	6 1/2	8000	1300	82
				21223-3	\$ ■ †	BC-EL/A R40 23W	Blister	2	6 1/2	8000	1250	82
				90	PAR38	Med.	15715-6	\$ ■ †	EL/A PAR38 23W	Box	6	6 1/2
21240-7	\$ ■ †	BC-EL/A PAR38 23W	Blister				2	6 1/2	8000	1250	82	
ENERGY SAVER DIMMABLE REFLECTOR FLOOD												
16	65	R30 Dim	Med.	13707-5	\$ ■	EL/A R30 16W DIMM	Box	6	5 1/2	8000	630	82
20	75	R40 Dim	Med.	13708-3	\$ ■	EL/A R40 20W DIMM	Box	6	6 1/2	8000	900	82
				PAR38 Dim	Med.	14644-9	\$ ■	EL/A PAR38 20W DIMM	Box	6	6 1/2	8000

For the most current product information, go to the e-catalog on www.philips.com
Compact fluorescent symbols and footnotes located on page 86

