

Fluorescent Lamps

Appliance, T9 4-Pin Circline

Nom. Lamp Watts	Product Number	Symbols, Footnotes	Ordering Code	Pkg. Qty. *	Description	Nom. Length (In.)	Rated Avg. Life, Hrs. (202)	Approx. Initial Lumens (203, 204)	Design Lumens (208)	CRI
Appliance Fluorescent Lamps T8 Medium Bipin Linear Fluorescent Lamps; For Use With Starters										
14	25914-3		F14T8/CW/I5	24	Cool White, 4100K	15	7500	700	595	62
16	25989-5		F16T8/CW/26	24	Cool White, 4100K	26	7500	1275	1020	62
17	25990-3		F17T8/CW/28	24	Cool White, 4100K	28	7500	1300	1030	62
18	38302-6		F18T8/CW/30/ALTO	24	Cool White, 4100K	30	7500	1350	1070	62
	36520-5		F18T8/CW/24	24	Cool White, 4100K	24	7500	1175	940	62

Appliance Fluorescent Lamps T12 Medium Bipin Linear Fluorescent Lamps; For Use With Starters										
25	14135-8		F25T12/CW/28	30	Cool White, 4100K	28	7500	1600	1280	62

Circline Fluorescent Lamps T9 4-Pin Circular Fluorescent Lamps										
20	24982-1		FC6T9/Cool White Plus	12	Cool White, 4100K	6 1/2 OD	12,000	800	590	62
22	39222-5		FC8T9/Soft White	12	3000K	8 OD	12,000	1150	875	85
	26234-5		FC8T9/D	12	Daylight, 6500K	8 1/4 OD	12,000	910	675	79
	39235-7		FC8T9/DayDLX	12	6500K	8 OD	12,000	910	675	79
	39116-9		FC8T9/Cool White Plus	12	Cool White, 4100K	8 OD	12,000	1050	775	62
32	39122-7		FC12T9/Soft White	12	3000K	12 OD	12,000	1900	1600	85
	26260-0		FC12T9/D	12	Daylight, 6500K	12 OD	12,000	1570	1300	79
	39117-7		FC12T9/Cool White Plus	12	Cool White, 4100K	12 OD	12,000	1800	1500	62
40	39118-5		FC16T9/Cool White Plus	12	Cool White, 4100K	16 OD	12,000	2500	1975	62

For the most current product information, go to the e-catalog on www.philips.com

Fluorescent symbols and footnotes located on page 87

 This product utilizes ALTO® Lamp Technology

For Black Light lamps, turn to page 111.