

T12 Fluorescent Lamps

Rapid Start, Advantage Rapid Start, Rapid Start "Long Life," Rapid Start 800, U-Bent

Nom. Lamp Watts	Product Number	Symbols, Footnotes	Ordering Code	Pkg. Qty. •	Description	Nom. Length (In.)	Rated Avg. Life, Hrs. (202)	Approx. Initial Lumens (203, 204)	Design Lumens (208)	CRI
Rapid Start Fluorescent Lamps T12 Medium Bipin										
25	27247-6	\$	F25T12/CW/RS/EW/ALTO	30	Cool White, 4100K	36	18,000	1950	1650	62
	31365-0	\$	F25T12/WW/RS/EW	30	Warm White, 3000K	36	18,000	2000	1700	53
30	31377-5		F30T12/30U/RS	30	Ultralume, 3000K	36	18,000	2400	2160	85
	31379-1		F30T12/35U/RS	30	Ultralume, 3500K	36	18,000	2400	2160	85
	31380-9	□	F30T12/41U/RS	30	Ultralume, 4100K	36	18,000	2400	2160	85
	31381-7	□	F30T12/50U/RS	30	Ultralume, 5000K	36	18,000	2380	2140	85
	31369-2		F30T12/SPEC30/RS	30	SPEC30, 3000K	36	18,000	2350	2080	70
	31371-8		F30T12/SPEC35/RS	30	SPEC35, 3500K	36	18,000	2350	2080	73
	31372-6		F30T12/SPEC41/RS	30	SPEC41, 4100K	36	18,000	2350	2080	70
	31376-7		F30T12/C50/RS	30	Colortone 50, 5000K	36	18,000	1550	1300	92
	37649-1		F30T12/D/RS/ALTO	30	Daylight, 6500K	36	18,000	1950	1700	79
	27242-7		F30T12/CW/RS/ALTO	30	Cool White, 4100K	36	18,000	2250	1900	62
31221-7		F30T12/WW/RS/ALTO	30	Warm White, 3000K	36	18,000	2300	1950	53	

Nom. Lamp Watts	Product Number	Symbols, Footnotes	Ordering Code	Pkg. Qty. •	Description	Nom. Length (In.)	Rated Avg. Life, Hrs. 3-Hr. Start (202)	Rated Avg. Life, Hrs. 12-Hr. Start (241)	Approx. Initial Lumens (203, 204)	Design Lumens (208)	CRI
Advantage Rapid Start Ultimate Performance Fluorescent Lamps T12 Medium Bipin											
NEW!	14257-0		F34T12/ADV30/EW/ALTO	30	Advantage 30,T12, 3000K	48	24,000	30,000	3100	2945	85
	14258-8		F34T12/ADV35/EW/ALTO	30	Advantage 35,T12, 3500K	48	24,000	30,000	3100	2945	85
	14259-6		F34T12/ADV41/EW/ALTO	30	Advantage 41,T12, 4100K	48	24,000	30,000	3100	2945	85
	14260-4		F34T12/ADV50/EW/ALTO	30	Advantage 50,T12, 5000K	48	24,000	30,000	3000	2845	85

Nom. Lamp Watts	Product Number	Symbols, Footnotes	Ordering Code	Pkg. Qty. •	Description	Nom. Length (In.)	Rated Avg. Life, Hrs. 3-Hr. Start (202)	Rated Avg. Life, Hrs. 12-Hr. Start (241)	Approx. Initial Lumens (203, 204)	Design Lumens (208)	CRI
Rapid Start "Long Life" Fluorescent Lamps T12 Medium Bipin											
NEW!	14251-3		F34/CW/RS/EW/LL/ALTO	30	Cool White, 4100K	48	24,000	30,000	2650	2300	62
	14252-1		F34/WW/RS/EW/LL/ALTO	30	Warm White, 3000K	48	24,000	30,000	2700	2350	53

Nom. Lamp Watts	Product Number	Symbols, Footnotes	Ordering Code	Pkg. Qty. •	Description	Nom. Length (In.)	Rated Avg. Life, Hrs. (202)	Approx. Initial Lumens (203, 204)	Design Lumens (208)	CRI
Rapid Start 800 Series Fluorescent Lamps T12 Medium Bipin										
NEW!	14253-9		F34T12/830/EW/ALTO	30	TL 830, 3000K	48	20,000	2800	2660	82
	14254-7		F34T12/835/EW/ALTO	30	TL 835, 3500K	48	20,000	2800	2660	82
	14255-4		F34T12/841/EW/ALTO	30	TL 841, 4100K	48	20,000	2800	2660	82
	14256-2		F34T12/850/EW/ALTO	30	TL 850, 5000K	48	20,000	2800	2660	82

Nom. Lamp Watts	Product Number	Symbols, Footnotes	Ordering Code	Pkg. Qty. •	Description	Nom. Length (In.)	Rated Avg. Life, Hrs. (202)	Approx. Initial Lumens (203, 204)	Design Lumens (208)	CRI
Rapid Start Fluorescent Lamps T12 Medium Bipin										
34	26659-3	\$	F34/DX/RS/EW/ALTO	30	Daylight Deluxe, 6500K	48	20,000	2025	1775	84
	24470-7	\$	F34/CW/RS/EW/ALTO	30	Cool White, 4100K	48	20,000	2650	2300	62
	22046-7	\$	F34/CW/RS/EW/ALTO	10	Cool White, 4100K, 10PK	48	20,000	2650	2300	62
	24472-3	\$	F34/CW/RS/EW/ALTO PLZ	650	Cool White, 4100K	48	20,000	2650	2650	62
	25686-7	\$	F34/WW/RS/EW/ALTO	30	Warm White, 3000K	48	20,000	2700	2350	53

Nom. Lamp Watts	Product Number	Symbols, Footnotes	Ordering Code	Pkg. Qty. •	Description	Nom. Length (In.)	Rated Avg. Life, Hrs. (202)	Approx. Initial Lumens (203, 204)	Design Lumens (208)	CRI
U-Bent Fluorescent Lamps T12 Medium Bipin										
34	37871-1	\$	FB34/SPEC30/6/EW/ALTO	12	SPEC30, 3000K	22 7/8	18,000	2760	2500	70
	37872-9	\$	FB34/SPEC35/6/EW/ALTO	12	SPEC35, 3500K	22 7/8	18,000	2760	2500	73
	37874-5	\$	FB34/SPEC41/6/EW/ALTO	12	SPEC41, 4100K	22 7/8	18,000	2760	2500	70
	37863-8		FB34/CW/6/EW/ALTO	12	Cool White, 4100K	22 7/8	18,000	2400	2050	62
	37865-3		FB34/LW/6/EW/ALTO	12	Lite White, 4200K	22 7/8	18,000	2500	2150	62
	37862-0		FB34/WW/6/EW/ALTO	12	Warm White, 3000K	22 7/8	18,000	2400	2050	53
	20704-3		FB34/CW/3/EW	12	Cool White, 4100K	22 7/8	18,000	2350	2050	62
	20705-0		FB34/WW/3/EW	12	Warm White, 3000K	22 7/8	18,000	2425	2125	51

For the most current product information, go to the e-catalog on www.philips.com

Fluorescent symbols and footnotes located on page 87

□ This product utilizes ALTO® Lamp Technology