

T12 Fluorescent Lamps

Advantage Rapid Start, Rapid Start 800, Rapid Start, U-Bent

Nom. Lamp Watts	Product Number	Symbols, Footnotes	Ordering Code	Pkg. Qty.	Description	Nom. Length (In.)	Rated Avg. Life, Hrs. (202)	Approx. Initial Lumens (203, 204)	Design Lumens (208)	CRI
-----------------	----------------	--------------------	---------------	-----------	-------------	-------------------	-----------------------------	-----------------------------------	---------------------	-----

Advantage Rapid Start Ultimate Performance Fluorescent Lamps T12 Medium Bipin Linear Fluorescent Lamps

40	26604-9	<input type="checkbox"/>	F40T12/ADV30/ALTO	30	Advantage 30,T12, 3000K	48	24,000	3600	3250	85
	26631-2	<input type="checkbox"/>	F40T12/ADV35/ALTO	30	Advantage 35,T12, 3500K	48	24,000	3600	3250	85
	26640-3	<input type="checkbox"/>	F40T12/ADV41/ALTO	30	Advantage 41,T12, 4100K	48	24,000	3600	3250	85
	26643-7	<input type="checkbox"/>	F40T12/ADV50/ALTO	30	Advantage 50,T12, 5000K	48	24,000	3600	3250	85

Rapid Start 800 Series Fluorescent Lamps T12 Medium Bipin

40	14261-2		F40T12/830/ALTO	30	TL 830, 3000K	48	20,000	3200	3040	82
	14262-0		F40T12/835/ALTO	30	TL 835, 3500K	48	20,000	3200	3040	82
	14263-8		F40T12/841/ALTO	30	TL 841, 4100K	48	20,000	3200	3040	82
	14264-6		F40T12/850/ALTO	30	TL 850, 5000K	48	20,000	2700	2900	82

NEW!

Rapid Start Fluorescent Lamps T12 Medium Bipin Linear Fluorescent Lamps

40	33464-9		F40/C75	30	Colortone 75, 7500K	48	20,000	2000	1720	95
	30203-4		F40/C50	30	Colortone 50, 5000K	48	20,000	2200	1915	92
	27359-9		F40/DX/ALTO	30	Daylight Deluxe, 6500K	48	20,000	2325	2025	84
	36765-6		F40/CWX	30	Cool White Deluxe, 4200K	48	20,000	2200	1800	89
	39228-2		F40/PLANT	6	Plant Light, Sleeved	48	20,000	1600	1360	—
	20189-7		F40/BB	6	Special Blue	48	20,000	550	385	—

U-Bent Fluorescent Lamps T12 Medium Bipin

40	37879-4		FB40/30U/6/ALTO	12	Ultralume, 3000K	22 7/16	18,000	3100	2850	85
	37840-6		FB40/35U/6/ALTO	12	Ultralume, 3500K	22 7/16	18,000	3100	2850	85
	37876-0		FB40/41U/6/ALTO	12	Ultralume, 4100K	22 7/16	18,000	3100	2850	85
	37866-1		FB40/SPEC30/6/ALTO	12	SPEC30, 3000K	22 7/16	18,000	3050	2775	70
	37854-7		FB40/SPEC35/6/ALTO	12	SPEC35, 3500K	22 7/16	18,000	3050	2775	73
	37868-7		FB40/SPEC41/6/ALTO	12	SPEC41, 4100K	22 7/16	18,000	3050	2775	70
	21993-1		FB40/DX/6	12	Daylight Deluxe, 6500K	22 7/16	18,000	2250	1950	84

For the most current product information, go to the e-catalog on www.philips.com

Fluorescent symbols and footnotes located on page 87

This product utilizes ALTO® Lamp Technology