

HALOGEN LAMPS

PAR20, PAR30L, PAR30S Lamps

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.‡	Description	Class, Filament	MOL (In.)	Rated Avg. Life (Hrs.)(93)	Approx. MBCP*	Lumens
-------	------	------	----------------	--------------------	---------------	-------	------------	-------------	-----------------	-----------	----------------------------	---------------	--------

HALOGEN PAR20 LAMPS 130V WISO REFLECTOR (82, 86)

50	PAR20	Med.	13846-1	\$	50PAR20/HAL/SP10	130	15	Spot 10° Ratings @ 120V=44W	C, CC-8	3%	2000 4000	4000 3320	550 420
			22921-1	\$	50PAR20/HAL/FL25	130	15	Flood 25° Ratings @ 120V=44W	C, CC-8	3%	2000 4000	1100 880	550 420

HALOGEN PAR30L LONG NECK LAMPS WISO REFLECTOR (82, 86)

50	PAR30L	Med.	22922-9	ⓔ	50PAR30L/HAL/SP10	120	15	Spot 10°	C, CC-8	4½	3000	5500	590
			22923-7	ⓔ	50PAR30L/HAL/WSP16	120	15	Wide Spot 16°	C, CC-8	4½	3000	3500	590
			22925-2	ⓔ	50PAR30L/HAL/FL25	120	15	Flood 25°	C, CC-8	4½	3000	2100	590
			22927-8	ⓔ	50PAR30L/HAL/WFL40	120	15	Wide Flood 40°	C, CC-8	4½	3000	950	590
75	PAR30L	Med.	22930-2	ⓔ	75PAR30L/HAL/SP10	120	15	Spot 10°	C, CC-8	4½	3000	12,300	1000
			22934-4	ⓔ	75PAR30L/HAL/WSP16	120	15	Wide Spot 16°	C, CC-8	4½	3000	6700	1000
			22941-9	ⓔ	75PAR30L/HAL/FL25	120	15	Flood 25°	C, CC-8	4½	3000	4100	1000
			22944-3	ⓔ	75PAR30L/HAL/WFL40	120	15	Wide Flood 40°	C, CC-8	4½	3000	1650	1000

HALOGEN PAR30L LONG NECK LAMPS 130V WISO REFLECTOR (82, 86)

50	PAR30L	Med.	22926-0	\$ⓔ	50PAR30L/HAL/FL25	130	15	Flood 25° Ratings @ 120V=44W	C, CC-8	4½	2000 4000	2300 1960	630 470
			22928-6	\$ⓔ	50PAR30L/HAL/WFL40	130	15	Wide Flood 40° Ratings @ 120V=44W	C, CC-8	4½	2000 4000	1050 840	630 470
75	PAR30L	Med.	13848-7	\$ⓔ	75PAR30L/HAL/SP10	130	15	Spot 10° Ratings @ 120V=66W	C, CC-8	4½	2500 5000	13,000 10,400	1050 780
			22943-5	\$ⓔ	75PAR30L/HAL/FL25	130	15	Flood 25° Ratings @ 120V=66W	C, CC-8	4½	2500 5000	4200 3360	1050 780
			22945-0	\$ⓔ	75PAR30L/HAL/WFL40	130	15	Wide Flood 40° Ratings @ 120V=66W	C, CC-8	4½	2500 5000	1750 1400	1050 780

HALOGEN PAR30S SHORT LAMPS WISO REFLECTOR (82, 86)

50	PAR30S	Med.	26349-1	ⓔ	50PAR30S/HAL/SP10	120	15	Spot 10°	C, CC-8	3%	3500	5800	610
			26358-2	ⓔ	50PAR30S/HAL/FL25	120	15	Flood 25°	C, CC-8	3%	3500	1800	610
			26364-0	ⓔ	50PAR30S/HAL/WFL40	120	15	Wide Flood 40°	C, CC-8	3%	3500	900	610
60	PAR30S	Med.	35751-7	ⓔ	60PAR30S/HAL/SP10	120	15	Spot 10°	C, CC-8	3%	3000	8000	800
			35753-3	ⓔ	60PAR30S/HAL/FL25	120	15	Flood 25°	C, CC-8	3%	3000	2500	800
			35758-2	ⓔ	60PAR30S/HAL/WFL40	120	15	Wide Flood 40°	C, CC-8	3%	3000	1250	800
75	PAR30S	Med.	28479-4	ⓔ	75PAR30S/HAL/SP10	120	15	Spot 10°	C, CC-8	3%	3500	9600	1050
			28488-5	ⓔ	75PAR30S/HAL/FL25	120	15	Flood 25°	C, CC-8	3%	3500	3850	1050
			28491-9	ⓔ	75PAR30S/HAL/WFL40	120	15	Wide Flood 40°	C, CC-8	3%	3500	1650	1050

HALOGEN ENERGY ADVANTAGE IR PAR30L LONG NECK LAMPS FEATURING HALOGEN INFRARED TECHNOLOGY AND WISO REFLECTOR (82, 86)

LOWER WATTAGE ENERGY SAVING LAMPS

50	PAR30L	Med.	23799-0	\$ⓔ †	50PAR30L/IRC/SP10	120	15	Spot 10°	C, CC-8	4½	4200	12,000	1000
			23429-4	\$ⓔ †	50PAR30L/IRC/FL25	120	15	Flood 25°	C, CC-8	4½	4200	3500	1000
			23800-6	\$ⓔ †	50PAR30L/IRC/WFL40	120	15	Wide Flood 40°	C, CC-8	4½	4200	1600	1000

For the most current product information, go to the e-catalog on www.philips.com
Halogen symbols and footnotes located on page 116

