



F32T8 TL741 ALTO

Keyword search

[+ Advanced search](#)


F32T8 TL741 ALTO

Lamp Description

Extra low mercury

- [Download product data sheet](#)
- [Print page](#)

[Product specs:](#)
[+ Images:](#)
[+ Family info:](#)

PRODUCT DATA

Product Number	272484
Full product name	F32T8 TL741 ALTO
Ordering Code	F32T8/TL741/ALTO
Pack type	1 Lamp
Pieces per Sku	1
Skus/Case	25
Pack UPC	046677272487
EAN2US	
Case Bar Code	50046677272482
Successor Product number	

General Characteristics

Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Green Base
Bulb	T8
Packing Type	1LP [1 Lamp]
Packing Configuration	25
Type	F32T8
Feature	ALTO II™
Ordering Code	F32T8/TL741/ALTO
Pack UPC	046677272487
Case Bar Code	50046677272482
Energy Saving	Energy Saving
Rated Avg Life [12-Hr Prog St]	36000 hr
Rated Avg Life [12-Hr Inst St]	30000 hr

Rated Avg Life [3-Hr Prog St]	30000 hr
Rated Avg Life [3-Hr Inst St]	24000 hr
Electrical Characteristics	
Watts	32W
Environmental Characteristics	
Mercury (Hg) Content	1.7 mg
Picogram per Lumen Hour	27 p/LuHr
Light Technical Characteristics	
Color Code	TL741 [CCT of 4100K]
Color Rendering Index	78 Ra8
Color Designation	TL741
Color Description	Cool White Plus
Color Temperature	4100 K
Initial Lumens	2800 Lm
Design Mean Lumens	2660 Lm
Product Dimensions	
Nominal Length [inch]	48
Logistic and Packing Data	
Product Number	272484

[Philips](#) | [Privacy policy](#) | [Terms of use](#)

©2004-2009 Koninklijke Philips Electronics N.V. All rights reserved.