

<b>Stock Code</b>	Philips_ES 5W 2700K
<b>Brand</b>	Philips
<b>Part No</b>	ES 5W 2700K
<b>Voltage (V)</b>	120
<b>Bulb Shape</b>	T2
<b>Base Type</b>	Medium (E26)
<b>Diameter (in)</b>	4.4
<b>Length (in)</b>	5.1
<b>Lumens (Initial)</b>	315
<b>Wattage (w)</b>	5
<b>Bulb Type</b>	Compact Fluorescent Lamp
<b>Life Hours</b>	10,000
<b>Color Temperature (K)</b>	2700
<b>CRI</b>	82
<b>Incandescent Equal (W)</b>	25
<b>Fixture Type</b>	Open or Enclosed