



MasterColor CDM-T T6 Elite

MasterColor CDM-T Elite 70W/930 T6 1CT

The Elite family is at the very top of the MasterColor CDM range, and gives a unique combination of unbeatable light quality and consistent performance over lifetime, while keeping running costs low. MasterColor metal halide lamps deliver consistent white light and higher color rendering than any standard metal halide source for architectural lighting.

Product data

• General Characteristics

Base	G12
Bulb	T6 [Diameter: 6/8 inch /19mm]
Bulb Finish	Clear
Operating Position	Universal [Any or Universal (U)]
Life to 5% failures EL	9000 hr
Life to 10% failures EL	10000 hr
Life to 20% failures EL	12000 hr
Avg. Life	15000 hr
Avg. Hrs. Life	15000 hr

• Light Technical Characteristics

Color Code	930 [CCT of 3000K]
Color Rendering Index	87 (min), 90 (nom) Ra8
Color Designation	Warm White
Color Temperature	3000 K
Color Temperature technical	2970 K
Initial Lumens	7500 Lm
Initial Lumens	7750 Lm
Luminous Efficacy Lamp EM	103 Lm/W
Luminous Efficacy Lamp EL	106 Lm/W
Lumen Maintenance EL 2000h	94 %
Lumen Maintenance EL 5000h	88 %
Lumen Maintenance EL 10000h	83 %
Lumen Maintenance EL 12000h	82 %

Design Mean Lumens EL	6730 Lm
Chromaticity Coordinate X	0.435 -
Chromaticity Coordinate Y	0.396 -

• Electrical Characteristics

System Power EL	80 W
Watts	70 W
Lamp Wattage	72 W
Lamp Wattage EL	73 W
Lamp Voltage	84 V
Lamp Current EM	1 A
Lamp Current EL	0.89 A
Ignition Time	30 (max) s
Run-up time 90%	3 (max) min
Re-ignition Time [min]	15 (max) min
Dimmable	No

• Environmental Characteristics

Energy Efficiency Label (EEL)	A+
Mercury (Hg) Content	6.6 mg
Energy consumption kWh/1000h	73 kWh

• UV-related Characteristics

Damage Factor D/fc PET (NIOSH)	0.2 (nom), 0.3 (max) - 8 (min), 64 (nom) h500lx
--------------------------------	---

PHILIPS

MasterColor CDM-T T6 Elite

• Luminaire Design Requirements

Cap-Base Temperature	250 (max) C
Pinch Temperature	350 (max) C
Bulb Temperature	500 (max) C

• Product Dimensions

Reference Length A	90 (max) mm
Overall Length C	103 (max) mm
Diameter D	20 (max) mm
Light Center Length L	55 (min), 56 (nom), 57 (max) mm
Arc Length O	7.15 mm
Light Center Length L	2.16 (min), 2.20 (nom), 2.24 (max) in
Max Overall Length (MOL) - C	4 (max) in

Diameter D 0.79 (max) in

• Product Data


Product number	409151
Full product name	MasterColor CDM-T Elite 70W/930 T6 1CT
Short product name	CDM70/T6/930 ELITE 12PK
Pieces per Sku	1
eop_pck_cfg	12
Skus/Case	12
Bar code on pack	46677409159
Bar code on case	50046677409154
Logistics code(s)	928185305115
eop_net_weight_pp	29.000 kg

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will


remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Dimensional drawing




MasterColor CDM-T Elite 70W/930 T6 1CT

Product	C (Max)	D (Max)	L (Min)	L (Norm)	L (Max)	O (Norm)
CDM-T ACCENT 70W/930 G12	103	20	55	56	57	7.15



G12

Photometric data



© 2013 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2013, August 8
data subject to change