

Globe - Medium Base

G25, G30, G40



- Ideal for general residential applications



G25

WHITE

120V

25G25WH2
40G25WH2

130V

25G25WH3
40G25WH3

G30

WHITE

125V

25G30WH
40G30WH

G40

WHITE

125V

25G40WH
40G40WH
60G40WH
100G40WH
150G40WH

G25

CLEAR

120V

25G25CL2
40G25CL2

130V

25G25CL3
40G25CL3

G40

CLEAR 125V

25G40CL
40G40CL
60G40CL
100G40CL
150G40CL

For CFL G25 & G30 alternatives, see pg 113; for Specialty alternatives see pg 40-47; for LED G25 alternatives, see Bulbrite's LED Catalog.

Watts	Bulb Type	Base	Item #	Ordering Code	Volts	Inner/Master	Description	Lumens	Average Hours	M.O.L.	Notes
25	G25	E26	330025	25G25WH3	130	24 / 120	White	115	3750	4.375"	1
			393002	25G25WH2	120	24 / 120	White	130	3000	4.375"	
			331025	25G25CL3	130	24 / 120	Clear	135	3750	4.375"	1
			393102	25G25CL2	120	24 / 120	Clear	150	3000	4.375"	
	G30	E26	340025	25G30WH	125	12 / 96	White	15	1500	5.125"	1
	G40	E26	350025	25G40WH	125	12 / 24	White	150	1500	6.75"	1
			351025	25G40CL	125	12 / 24	Clear	180	1500	6.75"	1
	40	G25	E26	330040	40G25WH3	130	24 / 120	White	225	3750	4.375"
393004				40G25WH2	120	24 / 120	White	280	3000	4.375"	
331040				40G25CL3	130	24 / 120	Clear	255	3750	4.375"	1
393104				40G25CL2	120	24 / 120	Clear	300	2500	4.375"	
	G30	E26	340040	40G30WH	125	12 / 96	White	300	1500	5.125"	1
	G40	E26	350040	40G40WH	125	12 / 24	White	300	1500	6.75"	1
			351040	40G30CL	125	12 / 24	Clear	340	1500	6.75"	1
60	G40	E26	350060	60G40WH	125	12 / 24	White	570	1500	6.75"	1
			351060	60G40CL	125	12 / 24	Clear	610	1500	6.75"	1
100	G40	E26	350100	100G40WH	125	12 / 24	White	1120	1500	6.75"	1
			351100	100G40CL	125	12 / 24	Clear	1200	1500	6.75"	1
150	G40	E26	350150	150G40WH	125	12 / 24	White	1600	1500	6.75"	1
			351150	150G40CL	125	12 / 24	Clear	1700	1500	6.75"	1

Lumens and Average Hours for 125V and 130V lamps are measured on a 120V line.