

COMPACT FLUORESCENT LAMPS

Energy Saver Twisters

Watts	Inc. Equiv. Watts	Bulb	Color Temp. (K)	Base	Product Number	Symbols, Footnotes	Description	Ordering Code	Pkg. Type	Case Qty.	MOL (In.)	Diam. (In.)	Rated Avg. Life (Hrs.) (230)	Approx. Initial Lumens (231)	CRI
9	40	T2 Twister	2700	Med.	40854-2	\$ + ■	Mini Twister Soft White	BC-EL/mdT2 9W	Clam	6	3 3/8	2	12,000	500	82
					40831-0	\$ + ■	Mini Twister Soft White	EL/mdT2 9W 4pk	Box	6	3 3/8	2	12,000	500	82
					41398-8	\$ + ■ +	Mini Twister Soft White	EL/mdT2 9W	Box	6	3 3/8	2	12,000	500	82
13	60	T2 Twister	2700	Med.	40855-9	\$ + ■	Mini Twister Soft White	BC-EL/mdT2 13W	Clam	6	3 3/8	2	12,000	840	82
					40832-8	\$ + ■	Mini Twister Soft White	EL/mdT2 13W 4pk	Box	6	3 3/8	2	12,000	840	82
					41399-6	\$ + ■ +	Mini Twister Soft White	EL/mdT2 13W	Box	6	3 3/8	2	12,000	840	82
18	75	T2 Twister	2700	Med.	40856-7	\$ + ■	Mini Twister Soft White	BC-EL/mdT2 18W	Clam	6	4 1/8	2 1/4	12,000	1250	82
					40833-6	\$ + ■	Mini Twister Soft White	EL/mdT2 18W 4pk	Box	6	4 1/8	2 1/4	12,000	1250	82
					41400-3	\$ + ■ +	Mini Twister Soft White	EL/mdT2 18W	Box	6	4 1/8	2 1/4	12,000	1250	82
23	100	T2 Twister	2700	Med.	40857-5	\$ + ■	Mini Twister Soft White	BC-EL/mdT2 23W	Clam	6	4 1/8	2 1/4	12,000	1600	82
					40834-4	\$ + ■	Mini Twister Soft White	EL/mdT2 23W 4pk	Box	6	4 1/8	2 1/4	12,000	1600	82
					41401-1	\$ + ■ +	Mini Twister Soft White	EL/mdT2 23W	Box	6	4 1/8	2 1/4	12,000	1600	82

ENERGY SAVERTWISTER

5	25	Twister	2700	Med.	14792-6	\$ ■	Twister Soft White	EL/mdT 5W	Box	6	3 3/8	1 1/8	12,000	315	82		
9	40	Twister	2700	Med.	14793-4	\$ ■	Twister Soft White	EL/mdT 9W	Box	6	4	1 1/8	12,000	550	82		
					40618-1	\$ + X ■	Twister Soft White	BC-EL/mdT 9W	Box	6	4	1 1/8	12,000	550	82		
					40619-9	\$ + X ■	Twister Soft White	EL/mdT 9W 4pk	Box	6	4	1 1/8	12,000	550	82		
11	40	Twister	2700	Med.	13804-0	\$ X ■	Twister Soft White	EL/mdT 11W	Box	6	4 3/8	1 1/8	10,000	700	82		
					13991-5	\$ ■	Twister Soft White	BC-EL/mdT 11W	Clam	6	4 3/8	1 1/8	10,000	700	82		
13	60	Twister	2700	Med.	15638-0	\$ ■	Twister Soft White	EL/mdT 13W	Box	6	4 3/8	1 1/8	10,000	900	82		
					40985-4	\$ +	Twister Soft White	Spiral 13W 12pk	Contr.	1	4 3/8	2	10,000	900	82		
					20907-2	\$ ■	Twister Soft White	BC-EL/mdT 13W	Clam	6	4 3/8	1 1/8	10,000	900	82		
					21929-5	\$ ■	Twister Soft White	BC-EL/mdT 13W 3PK	Clam	6	4 3/8	1 1/8	10,000	900	82		
					22782-7	\$ + X ■	Twister Soft White	EL/mdT 13W LL 4pk	Box	6	4 3/8	1 1/8	12,000	900	82		
					3500	Med.	22492-3	\$ +	Twister Warm White	EL/mdT 13W 3.5K	Box	6	4 3/8	1 1/8	10,000	900	82
					4100	Med.	21758-8	\$ ■	Twister Cool White	EL/mdT 13W 4K	Box	6	4 3/8	1 1/8	12,000	900	82
					5000	Med.	21759-6	\$ ■	Twister Bright White	EL/mdT 13W 5K	Box	6	4 3/8	1 1/8	12,000	900	82
					6500	Med.	22496-4	\$ + ■	Twister Daylight Deluxe	EL/mdT 13W 6.5K	Box	6	4 3/8	1 1/8	10,000	900	82
					6500	Med.	23537-4	\$ + ■	Twister Daylight Deluxe	BC-EL/mdT 13W 6.5K	Clam	6	4 3/8	1 1/8	10,000	900	82
14	60	Twister	Natural	Med.	21046-8	\$ +	Twister Soft White	BC-EL/mdT 14W Nat	Clam	6	4 3/8	1 1/8	10,000	650	82		
18	75	Twister	2700	Med.	20286-1	\$ ■	Twister Soft White	EL/mdT 18W	Box	6	5 1/8	2 3/8	12,000	1250	82		
					22767-8	\$ + X ■	Twister Soft White	BC-EL/mdT 18W LL	Clam	6	4 3/8	2 3/8	12,000	1200	82		
					22785-0	\$ + X ■	Twister Soft White	EL/mdT 18W LL	Box	6	4 3/8	2 3/8	12,000	1200	82		
19	75	Twister	2700	Med.	20909-8	\$ ■	Twister Soft White	BC-EL/mdT 19W	Clam	6	4 3/8	2 3/8	10,000	1200	82		
23	100	Twister	2700	Med.	15697-5	\$ ■	Twister Soft White	EL/mdT 23W	Box	6	4 3/8	2 3/8	12,000	1600	82		
					20910-6	\$ ■	Twister Soft White	BC-EL/mdT 23W	Clam	6	4 3/8	2 3/8	10,000	1600	82		
					20587-2	\$ ■	Twister Soft White	BC-EL/mdT 23W 3PK	Clam	6	4 3/8	2 3/8	10,000	1600	82		
					22769-4	\$ + X ■	Twister Soft White	BC-EL/mdT 23W LL	Clam	6	4 3/8	2 3/8	12,000	1600	82		
					22786-8	\$ + X ■	Twister Soft White	EL/mdT 23W 4PK LL	Box	6	4 3/8	2 3/8	12,000	1600	82		
					22789-2	\$ +	Twister Soft White	EL/mdT 23W 12pk	Contr.	1	4 3/8	2 3/8	10,000	1600	82		
					3500	Med.	22497-2	\$ + §	Twister Warm White	EL/mdT 23W 3.5K	Box	6	4 3/8	2 3/8	10,000	1600	82
					4100	Med.	22498-8	\$ + §	Twister Cool White	EL/mdT 23W 4.1K	Box	6	4 3/8	2 3/8	10,000	1500	82
					5000	Med.	22501-1	\$ + §	Twister Bright White	EL/mdT 23W 5K	Box	6	4 3/8	2 3/8	10,000	1500	82
					6500	Med.	22404-5	\$ + §	Twister Daylight Deluxe	EL/mdT 23W 6.5K	Box	6	4 3/8	2 3/8	10,000	1500	82

For the most current product information, go to the e-catalog on www.philips.com

Compact fluorescent symbols and footnotes located on page 69

+ Product will not be released until Spring 2011



9W T2 Mini Twister Med. 13W T2 Mini Twister Med. 18W T2 Mini Twister Med. 23W T2 Mini Twister Med. 5W Twister Med. 9W Twister Med. 11W Twister Med. 13W Twister Med. 14W Natural Light Twister Med. 18W Twister Med. 19W Twister Med. 23W Twister Med.