

INCANDESCENT LAMPS

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.‡	Description	Class Filament	LCL (In.)	MOL (In.)	Rated Avg. Life (Hrs.)(93)	Approx. MBCP*	Lumens
30	R20	Med.	22078-0	▲ (87)	30R20 12/1	130	12	Lt. Frost Reflector	C, CC-6		3 1/8	2000		205
			20181-4	▲ (87)	30R20/TG 120V 12/1	120	12	TuffGuard Coated Reflector Lamp	C, CC-6		3 1/8	2000		205
			20165-7	▲ (87)	30R20 12/1	120	12	Lt. Frost Reflector	C, CC-6		3 1/8	2000		205
			14597-8	□ (66)	30R20/SFL/TF	130	60	Frost Silicone Coated Reflector Sign	C, CC-6		3 1/8	6000		210
			16753-6	▲ (87)	30R20/LL 12/1	120	12	Frost Long Life Reflector	C, CC-6		3 1/8	2500	335	205
30 70 100	A21	3 Ct. Med.	16947-4	▲ (8)	30/100A/WL 12/1	120	12	Soft White Long Life 3-Way	C, 2CC-8		5 1/8	1750		285 920 1205
			36662-5	▲ (8)	30/100A/W 12/1	120	12	Soft White 3-Way	C, 2CC-8		5 1/8	1200		310 945 1255
34	A19	Med.	22234-9	▲ ✓ \$	40A-34A/EW	120	48	Frost Econ-o-watt	C, CC-6		4 1/8	1500		410
			22235-6	▲ \$	40A-34A/EW	130	48	Frost Econ-o-watt Ratings @ 120V = 30W	C, CC-6		4 1/8	1500	4245	400 305
38	A19	Med.*	21446-0		38A/CL/LL 12-2 WPTP	120	24	Clear Longer Life	C, CC-6		4 1/8	1500		420
			21443-7		38A/W/TP 12/4	120	48	Soft White	C, CC-6		4 1/8	1000		415
			21462-7		38A/W/TP 24/4	120	96	Soft White	C, CC-6		4 1/8	1000		415
			21444-5		38A/CL	130	48	Clear	C, CC-6		4 1/8	1500		420
			21447-8		38A/WL/TP 12/4	120	48	Soft White Longer Life	C, CC-6		4 1/8	1500		385
			21495-7		38A/WL 24/4	120	96	Soft White Longer Life	C, CC-6		4 1/8	1500		385
40	A15	Med.	29999-0	▲	BC40A15/CL/LL	120	12	Clear Longer Life Home Appliance	C, C-9		3 1/2	1750		400
			37398-5	▲	40A15	120-130	120	Frost Home Appliance	C, C-9		3 1/2	1000		415
			20182-2	▲	40A15/TG	120-130	120	TuffGuard Coated Frost Home Appliance	C, C-9		3 1/2	1000		415
			14073-1	▲	40A15/CL PRO	130	24	ProPack Clear	C, C-9		3 1/2	1000		415
			14963-3	▲ □ (66)	40A15/TF	120-130	120	Frost Refrigerator Silicone Coated	C, C-9		3 1/2	1000		
			16934-2	▲	BC40A15/FAN/CL/LL 6/2	120	12	Clear Long Life Fan	C, C-9		3 1/2	2000		395
			16935-9	▲	BC40A15/FAN/W/LL 6/2	120	12	White Long Life Fan	C, C-9		3 1/2	2000		365
			20002-2	▲	40A15/22	120	120	Clear Home Oven	C, C-9		3 1/2	1000		420
			13565-7	▲	BC40A15/FAN/N/TL 6/2	120	12	Natural Light Fan	C, C-9		3 1/2	1500		340
			A19	Med. ++	27081-9	▲	40A 12/4	120	48	Frost	C, CC-6		4 1/8	1500
	16797-2	▲			40A/CL/LL 12/2	120	24	Clear Long Life	C, CC-6		4 1/8	1500		505
	16737-9	▲			40A/WL 24/4	120	96	Soft White Long Life	C, CC-6		4 1/8	1500		475
	Med ++	16869-0		▲	40A/WL 12/4	120	48	Soft White Long Life	C, CC-6		4 1/8	1500		475
		13558-2		▲	40A/N/TL 12/4	120	48	Natural Light Standard	C, CC-6		4 1/8	1000		400
		37465-2		▲	40A	120	48	Frost	C, CC-6		4 1/8	1500		495
	Med ++	37466-0		▲	40A	130	48	Frost Ratings @ 120V = 35W	C, CC-6		4 1/8	1500	4245	490 375
		13993-1		▲	40A 120/1 PRO	130	120	Frost ProPack	C, CC-6		4 1/8	1500		490
		37399-3		▲	40A/CL	120-130	48	Clear Ratings @ 120V = 37W	C, CC-6	3 1/2	4 1/8	1500	2550	500 435
	Med	20183-0	▲	40A/CL/TG	120-130	48	TuffGuard Coated Clear	C, CC-6		4 1/8	1500		500	

For the most current product information, go to the e-catalog on www.philips.com
Incandescent symbols and footnotes located on page 149

