

INCANDESCENT LAMPS

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.†	Description	Class Filament	LCL (In.)	MOL (In.)	Rated Avg. Life (Hrs.)(93)	Approx. MBCP*	Lumens
3	S6	Cand.	37374-6	▲	3S6/5	120-130	48	Clear Indicator	B, C-7A		1½	3000		12
4	C-7	Cand.	25706-3	▲	BC4C7 12/2	120	24	Clear Night Light	B, C-7A		2½	3000		16
			24741-1	▲	BC4C7/4 12/4	120	48	Clear Night Light	B, C-7A		2½	3000		16
			25708-9	▲	BC4C7/W 12/2	120	24	White Night Light	B, C-7A		2½	3000		14
6	S6	Cand.	24835-1		6S6	120-130	48	Clear Indicator	B, C-7A		1½	1500		39
			23462-5		6S6	145	48	Clear Indicator	B, C-7A		1½	1500		37
			23476-5		6S6	155	48	Clear Indicator	B, C-7A		1½	1500		37
			23477-3		6S6/3	130	48	Clear Vibration	B, C-7A		1½	1500		18
		S6 Inter. D.C. Bay	37376-1		6S6DC	120-130	48	Clear Indicator	B, C-7A	1½	1½	1500		39
7	C-7	Cand.	37378-7	▲	7C7	120-130	24	Clear Indicator	B, C-7A		2½	3000		45
			25714-7	▲	BC7C7/W 12/2	120	24	White Night Light	B, C-7A		2½	3000		35
7½	S11	Med.	24811-2	▲	7½ S	120-130	24	Clear	B, C-7A		2½	1400		45
			37380-3	▲	7½ SW	120-130	24	White Night Light	B, C-7A		2½	1400		35
10	S6	Cand.	23485-6	▲	10S6/10	230	48	Clear Indicator	B, C-7A		1½	1500		65
			23488-0	▲	10S6/10	250	48	Clear Indicator	B, C-7A		1½	1500		65
	S11	Inter.	37381-1	▲	10S11N	120-130	24	Clear	B, C-7A	1½	2½	1500		70
	S14	Med.	13828-9		10S14/IF	130	24	Frost Sign	B, C-9		3½	1500		82
13829-7				10S14	120-130	24	Clear Sign	B, C-9		3½	1500		82	