

INCANDESCENT LAMPS

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.‡	Description	Class Filament	LCL (In.)	MOL (In.)	Rated Avg. Life (Hrs.)(93)	Approx. MBCP*	Lumens		
20	T6½	Inter.	24853-4		20T6-½IF	120	24	Frost Exit Sign	B, C-8		5½	5000		150		
	T6½	D.C. Bay	24839-3		20T6-½DC/IF	120	24	Frost Exit Sign	B, C-8		5½	5000		150		
			24838-5		20T6-½DC	120	24	Clear Exit Sign	B, C-8		5½	5000		160		
25	A15	Med.	14584-7	▲	25A15/I	120	60	Frost Refrigerator	B, C-9		3½	1000		210		
			16710-6	▲	BC25A15/IF 12/I	120	12	Frost Appliance	B, C-9		3½	1000		210		
			16868-2	▲	25A/WL 12/2	120	24	Soft White Long Life	C, CC-6		4⅞	3000		235		
			14421-2	▲	25A/TG 6/I	120	6	Transparent Green	B, C-9		3⅞	3000				
			14422-0	▲	25A/TR 6/I	120	6	Transparent Red	B, C-9		3⅞	3000				
			14423-8	▲	25A/TY 6/I	120	6	Transparent Yellow	B, C-9		3⅞	3000				
			14420-4	▲	25A/TB 6/I	120	6	Transparent Blue	B, C-9		3⅞	3000				
			14152-3	▲	25A	24	60	Frost	C, C-6		4⅞	1000		345		
			14153-1	▲	25A	34	60	Frost Train	C, C-6		4⅞	1000		325		
			25564-6	▲	25A/IF	120	48	Frost	C, CC-6		4⅞	2500		232		
	A19	Med.	20178-0		25A/IF/TG 24/2	130	48	TuffGuard Coated Lamp	C, CC-6		4⅞	2500				
			25566-1	▲	25A/IF	130	48	Frost	C, CC-6		4⅞	2500		232		
			25569-5	▲	25A/CL 24/2	120-130	48	Clear	C, CC-6		4⅞	2500		220		
			14973-2	▲	25A/TF	120	120	Frost Silicone Coated	B, C-9		3⅞	2500				
			14160-6	▲	25A/R	120	60	Red	B, C-9		3⅞	2500				
			14158-0	▲	25A/Y	120	60	Yellow	B, C-9		3⅞	2500				
			37386-0	▲	25A/RS	120-130	120	Frost Rough Service	R, C-9		3⅞	1000		235		
			37387-8	□	25A19/35	120-130	60	Frost Industrial Service	B, C-9		3⅞	3500		220		
			R14	Inter.	24828-6	■	R14N	120	24	Mini Refl. Lt. Fr. Actual Bulb Dia. 1¼"	C, CC-2V		2%	1500		200
					13336-3	■	BC25R14N 120V 6/I TP	120	6	Mini Refl. Lt. Fr.	C, CC-2V		3½	1500		150
T6½	Inter.	37388-6	▲	25T6-½IF	120-130	24	Frost Appliance	B, C-8		5½	1000		210			
		37389-4	▲	25T6-½	120-130	24	Clear Appliance	B, C-8		5½	1000		220			
T6½	D.C. Bay	37392-8		25T6-½DC	120-130	24	Clear Appliance	B, C-8		5½	1000		220			
T8	D.C. Bay	24827-8	(4)	25T8DC	120	24	Clear Appliance	B, C-7A		2%	1000		210			
T8	Inter.	23593-7	▲ (4)	25T8N	120	24	Clear Appliance	B, C-7A		2%	1000		220			
T10	Med.	39040-1	▲	BC25T10/IF/TP 6/I	120	6	Frost Showcase	B, C-8		5%	1000		245			
		13812-3	▲	25T10/IF 24/I	120-130	24	Frost Showcase	B, C-8		5%	1000		255			
		38985-8	▲	BC25T10/TP 6/I	120	6	Clear Showcase	B, C-8		5%	1000		250			
		13813-1	▲	25T10 24/I	120-130	24	Clear Showcase	B, C-8		5%	1000		260			
		20179-8	▲	25T10/TG	120-130	24	TuffGuard Coated Clear Showcase	B, C-8		5%	1000		260			

For the most current product information, go to the e-catalog on www.philips.com
Incandescent symbols and footnotes located on page 149

