



# PAR30/PAR20 LED

## 12PAR30L/AMB/F25/827/DIM ULW

Philips PAR30S LED Single Optic Lamps with AirFlux Technology provide superior lighting aesthetics and optimal thermal efficiency in a sleek, lightweight design.

### Product data

General Information	
Cap-Base	E26 [ Single Contact Medium Screw]
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	12-75W

Light Technical	
Color Code	827 [ CCT of 2700K]
Beam Angle (Nom)	25 °
Luminous Flux (Nom)	850 lm
Luminous Flux (Rated) (Nom)	850 lm
Luminous Intensity (Nom)	3300 cd
Color Designation	Warm White (WW)
Rated Beam Angle	25 °
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	70.83 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	12 W
Lamp Current (Nom)	110 mA

Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm Up Time To 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	85 °C

Controls and Dimming	
Dimmable	Yes

Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	Yes
Approval Marks	Energy Star

Product Data	
Order product name	12PAR30L/AMB/F25/827/DIM ULW
EAN/UPC - Product	046677467814
Order code	929001294004
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001294004


# PAR30/PAR20 LED

Net Weight (Piece)	0.285 kg
--------------------	----------

## Warnings and Safety

- Suitable for use in damp locations.
- Not for use in totally enclosed luminaires.
- Before replacing, turn off power and let lamp cool to avoid electrical shock or burn.
- CAUTION: Risk of electric shock— do not use where directly exposed to water
- NOTES: This device complies with Part 18 of the FCC rule. This product may cause interference with other devices. If interference occurs, change the location of the products involved. This RFLD device complies with Canadian ICES-005.



## Dimensional drawing



12PAR30L/AMB/F25/827/DIM ULW

Product	D	C
12PAR30L/AMB/F25/827/DIM ULW	95 mm	115 mm

## Photometric data



General Illumination 11 - PAR30 LED - Page 17

## PAR30/PAR20 LED

