



Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately.

Frame-In Kit	Ballast	Voltage	Lamp Type		Electrical	
					Input Wattage	Input Current
1102T1	NPF Magnetic	120V	2 Pin (Gx23)	13W Twin Tube	35W	.600A
1102TH1	HPF Magnetic	120V	2 Pin (Gx23)	13W Twin Tube	32W	.280A
1102TH2	HPF Magnetic	277V	2 Pin (Gx23)	13W Twin Tube	32W	.160A
1102TH1R (Remodel)*	HPF Magnetic	120V	2 Pin (Gx23)	13W Twin Tube	31W	.280A
1102T13U	HPF Electronic	120V/277V	4 Pin (G24q-1)	13W Quad Tube	33W	.28/.12A
1102T18U	HPF Electronic	120V/277V	4 Pin (G24q-2)	18W Quad Tube	40W	.34/.15A
1102T26U	HPF Electronic	120V/277V	4 Pin (G24q-3)	26W Quad Tube	56W	.47/.21A

Reflector Trims — See Individual Reflector Trim Specification Sheets

Alzak® Cone	Step Baffle	Cross Blade	Fresnel Lens	Enclosed Diffuser	Wall Washer
1113TGD 1113TCL	1105T 1105TWH	1132T	1126T	1128T 1178T	1135T 1135TWH

Features

- Mounting Frame:** #20 ga. galvanized steel. Accommodates ceiling up to 1" thick. Push-in/twist-out rotoclips hold reflector flush to ceiling.
- Junction Box:** #14 ga. galvanized steel. Rated for 8 #12 AWM through branch circuit wires suitable for 90° C, for end of run 75° C. Quick release "L" shaped cover for access to wiring. Integral cable clamps permit attachment of non-metallic Romex® or armored cable without the need for separate connectors.
- Mounting Bars:** Die-formed steel, 16 ga. Four bars, 13" long, extend to 27", permit off-center mounting; bars rotate 90° and lock in both directions; integral nailer for wood joists, locking tabs for T-bar runners.
- Socket Housing:** 22 ga. galvanized spring steel; snap-in quick assembly for precise lamp location.
- Socket:** Molded thermoplastic; prewired with #18 AWM leads to 4" X 3 1/2" X 2" junction box.
- Thermally Protected Ballast:** Single 2 lamp magnetic or universal voltage electronic, Class-P Rated. Insulation must be kept 3" away from fixture sides and wiring compartment and must not be placed above fixture as to entrap heat.

Options and Accessories

- Plaster Ceiling Ring:** 1961 - 7/8" depth for wet plaster ceiling.
- Remodeler Anchor Clip:** 1985S

Labels

UL (Suitable for Damp Locations), I.B.E.W.

Romex® is a registered trademark of General Cable Industries Inc.

Job Information	Type:
Job Name:	
Cat. No.:	
Lamp(s):	
Notes:	