

# BR LED with AirFlux Technology

# 10,5BR30/F90 2700 DIM AF 6/1

Philips BR Dimmable LED Lamps with AirFlux technology provide a soft, diffused level of light and smooth dimming to reduce glare. The sleek, lightweight design is ideal for downlighting.

#### Product data

#### • General Characteristics

Cap-Base E26
Bulb BR30
Rated Avg. Life (Hours) 25000 hr

# • Light Technical Characteristics

Color Code WW
Color Designation Warm White
Beam Angle 90 D
Correlated Color 2700 K

Temperature

CRI 81

Luminous Efficacy 69.52 Lm/W

Lamp

Color Temp. (Kelvin) 2700 K [CCT 2700K]

Rated Luminous Flux 730 Lm

# • Electrical Characteristics

Wattage	10.5 W
Wattage Technical	10.5 W
Voltage	120 V
Line Frequency	60 Hz
Power Factor	0.9 -
Lamp Current mA	93 mA
Dimmable	Yes
Wattage Equivalent	65 W

Starting Time 0.5 (max) s

# • Environmental characteristics

Energy consumption 11 kWh kWh/1000h

## • Measuring Conditions

Switching cycle 15000X

# • Product Dimensions

Overall Length C 131 mm Diameter D 95 mm

### • Product Data

 Product number
 293878

 Full product name
 10,58R30/F90 2700 DIM AF 6/1

 Short product name
 10.58R30/F90 2700 DIM AF 6/1

 Pieces per Sku
 1

 eop\_pck\_cfg
 6

 Skus/Case
 6

 Bar code on pack
 46677293871


Bar code on pack 46677293871
Bar code on case 50046677293876
Logistics code(s) 929000254404
eop\_net\_weight\_pp 0.275 kg





# BR LED with AirFlux Technology

# Dimensional drawing





E26



Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.