



Innovative design, irresistible price

SlimStyle A-Shape Dimmable LED

Philips SlimStyle A-Shape Dimmable LED Bulb is the same size as a traditional A19 light bulb in a new slim design. Its innovative shape is the same size as a traditional A19 light bulb in a new slim design. Its innovative shape provides energy efficiency and quality light in a durable shape.

Benefits

- Easy to experience - Provides soft, quality light similar to incandescents - Available in Soft White (2700K)
- Long life reduces the hassle of replacing bulbs so often ; Will not fade fabrics or furnishings
- Contains no mercury; Dimmable**
- Innovative design - Slim shape fits in most fixtures with a medium base
- Rugged design ensures durability and is ideal for households that want to provide a sense of security for their family
- Provides light all-around

Features

- Long lasting, energy efficient light
- Replaces 40 Watt and 60 Watt incandescent bulbs
- Last up to 22.8 years*
- Low yearly energy costs

Warnings and Safety

- Suitable for damp locations
- Not for use in totally enclosed luminaires (fixtures)
- This bulb is not intended for use with emergency exit fixtures or emergency lights.
- Before replacing, turn off power and let bulb cool to avoid electrical shock or burn.



PHILIPS

Related products




8 W, 10.5 W E26 A19




13 W E26 A21

Dimensional drawing



8A19/SLIM/2700 DIM 6/1

Product	C (Norm)	D (Norm)
LED 8-40W E26 2700K 120V A19	111.6	69
LED 10.5-60W E26 2700K 120V A19	111.6	69



13A21/SLIM/2700 DIM 120V 10/1


Product	C (Norm)	D (Norm)
LED 13W E26 2700K 120V A21	134	78

General Characteristics

Product number	Full product name	Cap-Base	Bulb	Rated Avg. Life (Hours)	Rated Avg. Life (Hours)
433672	8A19/SLIM/2700 DIM 6/1	E26	A19	25000 hr	25000 hr
433276	10.5A19/SLIM/2700 DIM 6/1	E26	A19	25000 hr	25000 hr

Product number	Full product name	Cap-Base	Bulb	Rated Avg. Life (Hours)	Rated Avg. Life (Hours)
452771	13A21/SLIM/2700 DIM 120V 10/1	E26	A21	25000 hr	25000 hr

Installation diagrams




E26

Light Technical Characteristics

Product number	Full product name	Color Code	Beam Description	Approximate Lumens	CRI	Color Temp. (Kelvin)	Rated Luminous Flux
433672	8A19/SLIM/2700 DIM 6/1	WW	-	450 Lm	80	2700 K	450 Lm
433276	10.5A19/SLIM/2700 DIM 6/1	WW	-	800 Lm	80	2700 K	800 Lm
452771	13A21/SLIM/2700 DIM 120V 10/1	WW	-	1100 Lm	80	2700 K	1100 Lm

Light technical



Electrical Characteristics

Product number	Full product name	Wattage	Voltage	Line Frequency	Dimmable	Wattage Equivalent	Starting Time
433672	8A19/SLIM/2700 DIM 6/1	8 W	120 V	60 Hz	Yes	40 W	0.5 (max) s
433276	10.5A19/SLIM/2700 DIM 6/1	10.5 W	120 V	60 Hz	Yes	60 W	0.5 (max) s
452771	13A21/SLIM/2700 DIM 120V 10/1	13 W	120 V	60 Hz	Yes	75 W	0.5 (max) s

Environmental characteristics

Product number	Full product name	Energy consumption kWh/1000h
433672	8A19/SLIM/2700 DIM 6/1	8 kWh
433276	10.5A19/SLIM/2700 DIM 6/1	11 kWh
452771	13A21/SLIM/2700 DIM 120V 10/1	13 kWh

Measuring Conditions

Product number	Full product name	Switching cycle
433672	8A19/SLIM/2700 DIM 6/1	50000X
433276	10.5A19/SLIM/2700 DIM 6/1	50000X
452771	13A21/SLIM/2700 DIM 120V 10/1	50000X



© 2014 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, November 18
data subject to change