

# COMPACT FLUORESCENT LAMPS

## Energy Saver Outdoor, Universal, TuffGuard Lamps

Watts	Inc. Equiv. Watts	Bulb	Color Temp. (K)	Base	Product Number	Symbols, Footnotes	Description	Ordering Code	Pkg. Type	Case Qty.	MOL (In.)	Diam. (In.)	Rated Avg. Life (Hrs.) (230)	Approx. Initial Lumens (231)	CRI
<b>ENERGY SAVER OUTDOOR</b>															
14	60	Twister	2700	Med.	40585-2	\$ + ■	Twister Photosensor	BC-EL/mdT D2D 14W	Clam	6	4 $\frac{3}{8}$	2 $\frac{1}{2}$	8000	820	82
		A19	Yellow	Med.	21214-2	\$	A19 Bug-A-Way	BC-EL/A SWP 14W BAW	Clam	4	4 $\frac{3}{8}$	2 $\frac{3}{8}$	8000	600	72
					20371-1	\$	A19 Bug-A-Way	EL/A SWP 14W BAW	Box	6	4 $\frac{3}{8}$	2 $\frac{3}{8}$	8000	600	72
		T20	2700	Med.	21246-4	\$ ■	Postlight	BC-EL/O 14W	Clam	4	5 $\frac{1}{8}$	2 $\frac{1}{2}$	8000	800	82
		T16	2700	Med.	40778-3	\$ + T	Prismatic Postlight	EL/O 14W Prisma	Box	6	5 $\frac{1}{8}$	2	8000	800	82
18	75	T16	2700	Med.	40580-3	\$ + ■	Prismatic Postlight	EL/O 18W Prisma	Box	6	6 $\frac{1}{8}$	2	8000	1100	82
<b>ENERGY SAVER UNIVERSAL</b>															
14	60	SLS	2700	Med.	14691-0	\$ ● ■	SLS Universal Triple Tube	SLS 14W	Box	6	5	2 $\frac{3}{8}$	12,000	860	82
20	75	SLS	2700	Med.	13077-3	\$ T ●	SLS Universal Triple Tube	SLS 20W	Box	6	5 $\frac{1}{8}$	2 $\frac{3}{8}$	15,000	1200	82
25	100	SLS	2700	Med.	13574-9	\$ T ●	SLS Universal Triple Tube	SLS 25W	Box	6	6 $\frac{1}{8}$	2 $\frac{3}{8}$	15,000	1750	82
<b>ENERGY SAVER TUFFGUARD</b>															
18	75	T20	2700	Med.	13578-0	\$ + ■	Tuff-Guard	EL/O 18W	Box	6	6	2 $\frac{3}{8}$	10,000	1100	82

For the most current product information, go to the e-catalog on [www.philips.com](http://www.philips.com)  
Compact fluorescent symbols and footnotes located on page 69



Twister Photosensor  
Med.



Bug-A-Way  
Med.



T20 Postlight  
Med.



T16 Prismatic Postlight  
Med.



14W SLS Universal  
Med.



20W SLS Universal  
Med.



25W SLS Universal  
Med.



18W Tuffguard T20  
Med.