

5-1/4" Aperture Incandescent Non-IC Remodeler Frame-In Kit




1003RS



## Complete fixture consists of Reflector Trim & Frame-in Kit. Select each separately

Frame-in Kit





## **Reflector Trim**

See Individual Reflector Trim Specification Sheets



## Features

Mounting Ring: .032 (#22 ga.) galvanized steel. Accommodates existing ceilings up to 2" thick. Attaches securely to any type of ceiling material without tools using (3) mounting straps provided. Push-in/twist-out clips hold reflector flush to ceiling. Includes adhesive backed aperture template.
Junction Box: 2 1/2" X 2 1/2" X 3 1/2" (21 cu. in.) .032 (#22 ga.) galvanized steel. cULus listed for 90° C supply wire. Integral cable clamps permit attachment of non-metallic (#12 or #14 ga.) Romex® cable without tools or additional connectors. Attaches to mounting ring without tools.

3. Socket Housing: Impact extruded aluminum or galvanized steel.

4. Socket: Porcelain medium base; nickel plated screw shell. Pre-wired with #18 ga. SF1 (300 VOLT 200° C) leads to junction box.

5. Thermal Protector: Meets NEC and U.L. requirements. Do not install insulation within 3 inches of fixture sides or wiring compartment nor above fixture in such a manner as to entrap heat.

Markings cULus listed, suitable for damp locations.

Job Information	Туре:	
Job Name:		
Cat. No.:		
Lamp(s):		
Notes:		

**LIGHTOLIER**