

CorePro LED

| Catalogue no. | Symbols | Description | Input Watts | Ballast/Voltage | Service Quantity | |
|---------------|---------|-------------|-------------|-----------------|------------------|---------|
| | | | | | 2 days | 10 days |

LED 4"

Trims - with attached LED light engine

| | | | | | | |
|---------|-----|-------------|---|-----------------------------|-----|--|
| CP430K6 | G • | White Splay | 8 | 600 lm/ 120V, Triac dimming | 100 | |
|---------|-----|-------------|---|-----------------------------|-----|--|

Frames

| | | | | | | |
|--------|--|-------------------------|--|------|-----|--|
| P4 | | Non-IC New Construction | | 120V | 70 | |
| P4ASIC | | IC New Construction | | 120V | 30 | |
| P4R | | Non-IC Remodeler | | 120V | 100 | |

LED 6"

Trims - with attached LED light engine

| | | | | | | |
|----------|-----|-------------|------|-----------------------------|-----|--|
| CP630K6 | G • | White Splay | 8.2 | 600 lm/ 120V, Triac dimming | 50 | |
| CP630K10 | G • | White Splay | 12.8 | 1000lm/120V, Triac dimming | 100 | |

Frames

| | | | | | | |
|------------|--|-----------------------------|--|------|-----|--|
| PR75ASICNB | | IC/AirSeal New Construction | | 120V | 50 | |
| CRR1NBQP | | IC Remodeler | | 120V | 100 | |

