

PHILIPS

LED

InstantFit LED T8 Lamps



Easily upgrade to LED from fluorescent.

Philips InstantFit LED T8 Lamps are an ideal energy saving choice for existing linear fluorescent fixtures.

Perfect for a wide range of applications

- Full light output in spaces with temperatures down to -4°F (-20°C)
- Perfect for applications with frequent “on/off” switching cycles
- Buildings that desire to be mercury free

Easy to experience

- Instant on, no flicker or buzz
- Fits into existing linear fixtures
- Optimized performance with Instant Start Ballasts¹
- Compatible with select Program Start Ballasts¹
- Eliminates the need for rewiring and allows the fixture to maintain original UL and CSA compliance²

Energy savings

- 41% energy savings vs F32T8 electronic instant start systems³

Easy to experience

- No mercury allowing for non-hazardous waste disposal
- Emits virtually no UV rays or IR
- Glass-free for use in food areas and refrigerated food displays
- 5-year limited warranty⁴

Footnotes on the page 3.

Philips InstantFit LED T8 Lamps

Ordering, Electrical and Technical Data (Subject to change without notice)


Product No.	Model No.	Ordering Code	Volts (Depending on Ballast)	Base	CRI	Color Temp. (K)	Pkg Qty	Rated Avg. Life ⁵	MOL (In.)	Beam Angle
LED InstantFit T8 - 4'										
45358-9	9290011239	12T8/48-3000 IF 10/1	120-277, 347	G13	82	3000	10	50,000	48	160
● 45359-7	9290011240	12T8/48-3500 IF 10/1	120-277, 347	G13	82	3500	10	50,000	48	160
● 45360-5	9290011241	12T8/48-4000 IF 10/1	120-277, 347	G13	82	4000	10	50,000	48	160
● 45361-3	9290011242	12T8/48-5000 IF 10/1	120-277, 347	G13	82	5000	10	50,000	48	160
LED InstantFit T8 - 4' High Output										
● 43486-0	9290002880	16.5T8/48-3000 IF 10/1	120-277, 347	G13	82	3000	10	50,000	48	160
● 43487-8	9290002881	16.5T8/48-3500 IF 10/1	120-277, 347	G13	82	3500	10	50,000	48	160
● 43488-6	9290002882	16.5T8/48-4000 IF 10/1	120-277, 347	G13	82	4000	10	50,000	48	160
● 43489-4	9290002883	16.5T8/48-5000 IF 10/1	120-277, 347	G13	82	5000	10	50,000	48	160
LED InstantFit T8 - 3'										
45205-2	9290011183	10.5T8/36-3000 IF 10/1	120-277, 347	G13	82	3000	10	50,000	36	160
45206-0	9290011184	10.5T8/36-3500 IF 10/1	120-277, 347	G13	82	3500	10	50,000	36	160
45207-8	9290011185	10.5T8/36-4000 IF 10/1	120-277, 347	G13	82	4000	10	50,000	36	160
45208-6	9290011186	10.5T8/36-5000 IF 10/1	120-277, 347	G13	82	5000	10	50,000	36	160
LED InstantFit T8 - 2' High Output										
45201-1	9290011179	8.5T8/24-3000 IF 10/1	120-277, 347	G13	82	3000	10	50,000	24	160
● 45202-9	9290011180	8.5T8/24-3500 IF 10/1	120-277, 347	G13	82	3500	10	50,000	24	160
● 45203-7	9290011181	8.5T8/24-4000 IF 10/1	120-277, 347	G13	82	4000	10	50,000	24	160
● 45204-5	9290011182	8.5T8/24-5000 IF 10/1	120-277, 347	G13	82	5000	10	50,000	24	160
LED InstantFit T8 U-Bent- 6" High Output										
45266-4	9290011196	16.5T8/22.5-3000 IF-6U 10/1	120-277, 347	G13	82	3000	10	50,000	22.5	160
45267-2	9290011197	16.5T8/22.5-3500 IF-6U 10/1	120-277, 347	G13	82	3500	10	50,000	22.5	160
45268-0	9290011198	16.5T8/22.5-4000 IF-6U 10/1	120-277, 347	G13	82	4000	10	50,000	22.5	160
45269-8	9290011199	16.5T8/22.5-5000 IF-6U 10/1	120-277, 347	G13	82	5000	10	50,000	22.5	160

Ballast Compatibility Guide

Please refer to www.philips.com/instantfit for instant start ballasts details and the latest ballast compatibility guide.

Relative Light Output vs. Ambient Temperature

4' T8 Lamps - 0.88 BF Ballast



— 25W — 28W — 32W T8 — 14.5W InstantFit TLED
Relative light output with respect to 25°C rated temperature

Suitable for use in fixtures where ambient temperature is between -4°F (-20°C) and 113°F (45°C).

Warning: Philips LED T8 InstantFit lamps will only operate properly on compatible Instant-start and Programmed-start ballasts. Please refer to the Philips LED T8 InstantFit Installation Guide, which can be obtained through your local Philips Sales Representative, or visit www.philips.com/instantfit

FCC Note: This device complies with Part 18 of the FCC Rules.

Philips InstantFit LED T8 Lamps

Ordering, Electrical and Technical Data (Subject to change without notice)

Product No.	Bare Lamp Watts (W)	Average System Watts (W)			Initial Lumens ⁶		
		Low Ballast Factor (0.78)	Normal Ballast Factor (0.88)	High Ballast Factor (1.18)	Low Ballast Factor (0.78)	Normal Ballast Factor (0.88)	High Ballast Factor (1.18)
LED InstantFit T8 - 4'							
45358-9	12	12.5	14.5	18.5	1300	1500	1700
45359-7	12	12.5	14.5	18.5	1300	1500	1800
45360-5	12	12.5	14.5	18.5	1400	1600	1850
45361-3	12	12.5	14.5	18.5	1450	1650	2000
LED InstantFit T8 - 4' High Output							
43486-0	16.5	17.5	19	25.5	1800	2000	2700
43487-8	16.5	17.5	19	25.5	1800	2000	2700
43488-6	16.5	17.5	19	25.5	1900	2100	2800
43489-4	16.5	17.5	19	25.5	1950	2150	2900
LED InstantFit T8 - 3'							
45205-2	10.5	12.5	13	17	1000	1100	1330
45206-0	10.5	12.5	13	17	1050	1160	1400
45207-8	10.5	12.5	13	17	1080	1200	1440
45208-6	10.5	12.5	13	17	1150	1270	1550
LED InstantFit T8 - 2' High Output							
45201-1	8.5	10	10.5	14.5	860	950	1110
45202-9	8.5	10	10.5	14.5	900	1040	1170
45203-7	8.5	10	10.5	14.5	930	1050	1200
45204-5	8.5	10	10.5	14.5	1000	1100	1290
LED InstantFit T8 U-Bent- 6" High Output							
45266-4	16.5	17.5	19	25.5	1800	2000	2700
45267-2	16.5	17.5	19	25.5	1800	2000	2700
45268-0	16.5	17.5	19	25.5	1900	2100	2800
45269-8	16.5	17.5	19	25.5	1950	2150	2900

- Please refer to the InstantFit ballast compatibility guide @ www.philips.com/instantfit. Compatibility subject to change as additional ballasts are tested. If you do not see your ballast on the compatibility list please contact your local Philips Lighting representative.
 - Must follow guidelines for installation from Philips Quick Installation Guide included with lamp shipment.
 - (2) Lamp F32T8 Electronic Instant Start System with 0.88 Ballast Factor= 58 System Watts; (2) Philips LED T8 InstantFit =29 System Watts; 58 - 29 = 29 System Watts Saved; 29/58 = 50% Energy Saved
 - See warranty for terms and conditions at www.philips.com/warranties
 - Tested to B50 L70 requirement.
 - Photometric testing consistent with IES LM-79.
- This lamp is DLC qualified.

System Power Compatibility Guide

This chart shows the measured system wattage of the Philips InstantFit TLED versus a comparable linear fluorescent lamp when used with the reference ballast.

	Reference Ballast	ICN-1P32-N	ICN-2P32-N	ICN-3P32-N	ICN-4P32-N
	Ballast Factor	0.88	0.88	0.88	0.88
	Number of Lamps	1	2	3	4
Specification	Lamp Type	System Power (W)			
	F32T8	31	59	85	112
	InstantFit 12 W	12.5	27.5	40	58
	InstantFit 16.5 W	19	38	57	76

* Variance <10%

Philips InstantFit LED T8 Lamps

Shipping Data (Subject to change without notice)

Product Number	SKU UPC (0-46677)	Outer Bar Code (5-00-46677)	Case Qty.	Case Weight (lbs.)	Case Cube (cu. Ft.)	Pallet Qty	Lamps/SKU	SKUs per Layer	Layers High	SKU Dimensions (W x D x H) (In.)	Case Dimensions (W x D x H) (In.)	Pallet Dimensions (W x D x H) (In.)
LED InstantFit T8 - 4'												
45358-9	45358-9	45358-4	10	4.6	.59	600	1	60	10	1.1x1.1x48.0	48.8 x 6.0 x 3.5	49.2 x 39.4 x 40.9
45359-7	45359-6	45359-1	10	4.6	.59	600	1	60	10	1.1x1.1x48.0	48.8 x 6.0 x 3.5	49.2 x 39.4 x 40.9
45360-5	45360-2	45360-7	10	4.6	.59	600	1	60	10	1.1x1.1x48.0	48.8 x 6.0 x 3.5	49.2 x 39.4 x 40.9
45361-3	45361-9	45361-4	10	4.6	.59	600	1	60	10	1.1x1.1x48.0	48.8 x 6.0 x 3.5	49.2 x 39.4 x 40.9
LED InstantFit T8 - 4' High Output												
43486-0	43486-1	43486-6	10	4.6	.43	600	1	60	10	1.1x1.1x48.0	48.8 x 6.0 x 3.5	49.2 x 39.4 x 40.9
43487-8	43487-8	43487-3	10	4.6	.43	600	1	60	10	1.1x1.1x48.0	48.8 x 6.0 x 3.5	49.2 x 39.4 x 40.9
43488-6	43488-6	43488-0	10	4.6	.43	600	1	60	10	1.1x1.1x48.0	48.8 x 6.0 x 3.5	49.2 x 39.4 x 40.9
43489-4	43489-2	43489-7	10	4.6	.43	600	1	60	10	1.1x1.1x48.0	48.8 x 6.0 x 3.5	49.2 x 39.4 x 40.9
LED InstantFit T8 - 3'												
45205-2	45205-6	45205-1	10	4.63	.43	700	1	70	10	1.1x1.1x36.0	36.5 x 6.0 x 3.4	47.2 x 39.4 x 39.6
45206-0	45206-3	45206-8	10	4.63	.43	700	1	70	10	1.1x1.1x36.0	36.5 x 6.0 x 3.4	47.2 x 39.4 x 39.6
45207-8	45207-0	45207-5	10	4.63	.43	700	1	70	10	1.1x1.1x36.0	36.5 x 6.0 x 3.4	47.2 x 39.4 x 39.6
45208-6	45208-7	45208-2	10	4.63	.43	700	1	70	10	1.1x1.1x36.0	36.5 x 6.0 x 3.4	47.2 x 39.4 x 39.6
LED InstantFit T8 - 2' High Output												
45201-1	45201-8	45201-3	10	4.63	.43	700	1	70	10	1.1x1.1x36.0	36.5 x 6.0 x 3.4	47.2 x 39.4 x 39.6
45202-9	45202-5	45202-0	10	4.63	.43	700	1	70	10	1.1x1.1x36.0	36.5 x 6.0 x 3.4	47.2 x 39.4 x 39.6
45203-7	45203-2	45203-7	10	4.63	.43	700	1	70	10	1.1x1.1x36.0	36.5 x 6.0 x 3.4	47.2 x 39.4 x 39.6
45204-5	45204-9	45204-4	10	4.63	.43	700	1	70	10	1.1x1.1x36.0	36.5 x 6.0 x 3.4	47.2 x 39.4 x 39.6
LED InstantFit T8 U-Bent- 6" High Output												
45266-4	45266-7	45266-2	10	5.95	1.19	300	1	100	3	1.1x7.2x23.0	23.1 x 7.5 x 11.9	47.2 x 39.4 x 41.4
45267-2	45267-4	45267-9	10	5.95	1.19	300	1	100	3	1.1x7.2x23.0	23.1 x 7.5 x 11.9	47.2 x 39.4 x 41.4
45268-0	45268-1	45268-6	10	5.95	1.19	300	1	100	3	1.1x7.2x23.0	23.1 x 7.5 x 11.9	47.2 x 39.4 x 41.4
45269-8	45269-8	45269-3	10	5.95	1.19	300	1	100	3	1.1x7.2x23.0	23.1 x 7.5 x 11.9	47.2 x 39.4 x 41.4



© 2014 Koninklijke Philips N.V. All rights reserved.
Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting, North America Corporation
200 Franklin Square Drive, Somerset, NJ 08873
Tel. 855-486-2216

Imported by: Philips Lighting,
A division of Philips Electronics Ltd.
281 Hillmount Rd, Markham, ON, Canada L6C 2S3
Tel. 800-668-9008