



LED T8 InstantFit Lamp

12T8/48-4000 IF 10/1

Philips LED T8 InstantFit Lamps are an ideal energy saving choice for existing linear fluorescent fixtures.

Product data

• General Characteristics

Main Application	Industrial
Cap-Base	G13
Rated Avg. Life (Hours)	40000 hr
Nominal Lifetime hours	40000 hr
B50L70	40000

• Light Technical Characteristics

Color Code	840
Beam Angle	160 D
Correlated Color Temperature	4000 K
CRI	83
Rated Luminous Flux	1600 Lm
LLMF - end nominal lifetime	70 %
Colour consistency	<6
Rated Beam Angle	160 D

• Electrical Characteristics

Wattage	12 W
Voltage	120-277 V
Line Frequency	50/60 Hz
Power Factor	0.9 (min) -
Dimmable	No
Rated Wattage	12.0 W
Starting Time	0.5 (max) s
Lamp voltage	120-277 V
Warm-up Time to 60% Light Outp	instant full light
Energy saving product	Yes

Suitable for accent lighting No

• Temperature Characteristics

T-case maximum	42 (max) C
Operating temperature	-20 (min), 45 (max) C
T-Storage	-45 (min), 65 (max) C

• Environmental characteristics

Energy Efficiency Label (EEL)	A+
Energy consumption kWh/1000h	14.5 kWh

• Measuring Conditions

Switching cycle	50000X
-----------------	--------

• Product Dimensions

Length A1	1198.0 mm
Fixing Hole Distance A2 Length	1205.0 mm
Length A3	1212.0 mm
Mounting hole diameter	25.68 mm
Circular outline dimension	28 mm

• Approval & Application Chars

VDE marking	No
CE marking	Yes
UL certificate	Yes



PHILIPS

LED T8 InstantFit Lamp


RoHS compliance Yes
 KEMA Keur certificate Yes

Short product name 12T8/48-4000 IF 10/1
 Pieces per Sku 1
 eop_pck_cfg 10
 Skus/Case 10
 Bar code on pack 46677453602
 Bar code on case 50046677453607
 Logistics code(s) 929001124104
 eop_net_weight_pp 0.360 kg

• Product Data


Product number 453605
 Full product name 12T8/48-4000 IF 10/1

Dimensional drawing



12T8/48-4000 IF 10/1

Product	A (Norm)	A1 (Norm)	A2 (Norm)	A3 (Norm)	B (Min)	B (Norm)	B (Max)	D (Min)	D (Norm)	D (Max)	D1 (Norm)	D2 (Norm)
LEDtube 1200mm 12W G13/840	-	1198.0	1205.0	1212.0	-	-	-	-	-	-	25.68	28



G13



© 2015 Koninklijke Philips N.V. (Royal Philips)
 All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2015, February 1
 data subject to change