



T8 Standard

F25T8/TL841 ALTO

Philips T8 lamps are energy-efficient lighting solutions.

Product data

• General Characteristics

Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Green Base
Bulb	T8
Energy Saving	Energy Saving
Rated Avg Life [12-Hr Prog St]	36000 hr
Rated Avg Life [12-Hr Inst St]	30000 hr
Rated Avg Life [3-Hr Prog St]	30000 hr
Rated Avg Life [3-Hr Inst St]	24000 hr

• Light Technical Characteristics

Color Code	TL841 [CCT of 4100K]
Color Rendering Index	85 Ra8
Color Designation	TL841
Color Temperature	4100 K
Initial lumen	2150 Lm
Design Mean Lumens	2045 Lm

• Electrical Characteristics

Watts	25 W
-------	------

• Environmental Characteristics

Mercury (Hg) Content	1.7 mg
Picogram per Lumen Hour	35 p/LuHr

• Product Dimensions


Nominal Length [inch]	36
-----------------------	----

• Product Data


Product number	281915
Full product name	F25T8/TL841 ALTO
Short product name	F25T8/TL841/ALTO 30PK
Pieces per Sku	1
eop_pck_cfg	30
Skus/Case	30
Bar code on pack	46677281915
Bar code on case	50046677281910
Logistics code(s)	927851084102
eop_net_weight_pp	0.001 kg

PHILIPS

Dimensional drawing



G13



F25T8/TL841 ALTO



© 2015 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2015, July 15
data subject to change