

PL-T Triple 4-Pin Base

PL-T 32W/835/4P 1CT

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Product data

• General Characteristics

Base	GX24q-3
Base Information	4P
Avg. Hrs. Life	16000 hr

• Light Technical Characteristics

Color Code	835 [CCT of 3500K]
Color Rendering Index	82 Ra8
Color Designation	White
Color Temperature	3500 K
Initial Lumens	2400 Lm
Luminous Efficacy Lamp EL	75 Lm/W
Lumen Maintenance EL 2000h	93 %
Lumen Maintenance EL 5000h	86 %
Lumen Maintenance EL 10000h	79 %
Chromaticity Coordinate X	411 -
Chromaticity Coordinate Y	398 -

• Electrical Characteristics

Watts	32 W
-------	------

Lamp Wattage EL	29.0 W
Lamp Voltage EL	125 V
Lamp Current EL	0.320 A
Dimmable	Yes

• Product Dimensions

Base Face to Base Face A	102 (max) mm
Insertion Length B	126.5 (max) mm
Overall Length C	141.4 (max) mm
Diameter D	41 (max) mm
Diameter D1	41 (max) mm

• Product Data

Product number	268334
Full product name	PL-T 32W/835/4P 1CT
Short product name	PL-T 32W/35/4P/ALTO 12PK
Pieces per Sku	1
eop_pck_cfg	12
Skus/Case	12
Bar code on pack	46677268336
Bar code on case	50046677268331
Logistics code(s)	927911883513
tpd_ilcos_cd	FSM-32/35/1B-E-GX24q=3
eop_net_weight_pp	82.000 gr