

Twistline GU10

BC50 TWISTLINE GU10/FL 6/3

Bright, white accent light with superior energy savingsPhilips Twistline GU10 Philips Halogen Twistline MR16 with GU10 base provide bright white accent light. The twist and lock base enables easy installation and a secure fit. Suited for track and recessed lighting applications.

Product data

• General Information

Cap-Base GU10 [GU10]
Bulb Shape MR16 [2inch/50mm]
Operating Position UNIVERSAL [Any or Universal (U)]
Nominal Lifetime (Nom)

• Light Technical

Beam Angle (Nom) 25 °
Luminous Intensity 700 cd (Max)
Correlated Color 2800 K
Temperature (Nom)
Color Rendering 100
Index (Nom)

Operating and Electrical

 Power (Rated)
 50 W

 (Nom)
 Starting Time (Nom)
 0.0 s

 Voltage (Nom)
 120 V

• Controls and Dimming

Dimmable Yes

• Mechanical and Housing

Bulb Finish Clear

• Approval and Application


Energy Efficiency Label (EEL)

• Product Data

Order product name EAN/UPC - Product 50046677208689
Order code 925691836305
Numerator - Quantity Per Pack
Numerator - Packs per outer box Material Nr. (12NC)
Net Weight (Piece) BC50 TWISTLINE GU10/FL 6/3
50046677208689
925691836305
1
6
925691836305
0.046 kg




Dimensional drawing



TWIST 50W GU10 120V 25D

Product	D	С
BC50 TWISTLINE GU10/FL 6/3	51 mm	53 mm





© 2016 Philips Lighting Holding B.V. All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.