



PAR38 LED

13.5PAR38/AMB/F40/830/DIM ULW

Philips PAR38 LED Single Optic Lamps with AirFlux Technology improves shopping experience with superior lighting aesthetics and optimal thermal efficiency in a sleek, lightweight design.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Bulb Shape	PAR38 [PAR 4.75 inch/121mm]
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	13.5-90W
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	40 °
Initial lumen (Nom)	950 lm
Luminous Flux (Rated) (Nom)	950 lm
Luminous Intensity (Nom)	1700 cd
Color Designation	White (WH)
Rated Beam Angle	40 °
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	70.37 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz


Power (Rated) (Nom)	13.5 W
Lamp Current (Nom)	119 mA
Wattage Equivalent	90 W
Starting Time (Nom)	0.5 s
Warm Up Time To 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	65 °C
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	Yes
Approbation Marks	Energy Star
Product Data	
Order product name	13.5PAR38/AMB/F40/830/DIM ULW
EAN/UPC - Product	046677467791
Order code	467795

PAR38 LED

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001292504

Net Weight (Piece)	0.385 kg
--------------------	----------

Dimensional drawing



13.5PAR38/AMB/F40/830/DIM ULW

Product	D	C
---------	---	---




PAR38 LED

Photometric data

Accent Lighting - Spots

1 x PAR38 13.5W3000K40D 9290012925

1 x 950 lm




Light output ratio 1.00
 Service upward 0.00
 Service downward 1.00

I_{max} 2064 cd

BS (1/2 I_{max}) 2 x 18°
 BS (1/2 E₀) 2 x 17°

Visual impact diagram



2016-09-27

PAR38 LED

