



# Preheat T12

F20T12 CW ALTO

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

## Product data

### • General Characteristics

Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Green Base
Bulb	T12
Rated Avg. Life [3 hr Start]	9000 hr

### • Light Technical Characteristics

Color Code	33
Color Rendering Index	62 Ra8
Color Designation	Cool White
Color Temperature	4100 K
Initial lumen	1200 Lm
Design Mean Lumens	1050 Lm

### • Electrical Characteristics

Watts	20 W
-------	------

### • Environmental Characteristics

Mercury (Hg) Content	1.9 mg
----------------------	--------

### • Product Dimensions


Nominal Length [inch]	24
-----------------------	----

### • Product Data


Product number	273326
Full product name	F20T12 CW ALTO
Short product name	F20T12 CW ALTO/30
Pieces per Sku	1
eop_pck_cfg	30
Skus/Case	30
Bar code on pack	46677273323
Bar code on case	50046677273328
Logistics code(s)	927883003301
eop_net_weight_pp	0.001 kg

# PHILIPS


Dimensional drawing



F20T12 CW ALTO



G13



F20T12 CW ALTO



© 2013 Koninklijke Philips N.V. (Royal Philips)  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2013, July 9  
data subject to change