



A-Shape LED

17A21/END/2700 DIM 6/1

Philips A-shape Dimmable LED lamps are the smart LED alternative to standard incandescents. The unique lamp design provides omi-directional light with excellent dimming performance.

Données du produit

• Caractéristiques Générales

Cap-Base	E26
Bulb	A21
Rated Avg. Life (Hours)	25000 hr

• Caractéristiques techn. de lumière

Color Code	WW
Color Designation	Warm White
Correlated Color Temperature	2700 K
CRI	80
Color Temp. (Kelvin)	2700 K [CCT 2700K]
Rated Luminous Flux	1100 Lm

• Caractéristiques électriques

Wattage	17 W
Wattage Technical	17.0 W
Voltage	120 V
Power Factor	0.71 -
Lamp Current mA	195 mA
Dimmable	Yes

• Caractéristiques environnementales

Energy Efficiency Label (EEL)	A
-------------------------------	---

• Dimensions en mm.

Overall Length C [inch]	5.039 (max) in
-------------------------	----------------

• Données produit

Code commercial	418590
Code produit EOC	418590
Nom produit	17A21/END/2700 DIM 6/1
Désignation	17A21/END/2700-1100 DIM 6/1
Pièces par pack	1
Config. Emballage	6
Packs par carton	6
Code barre produit	46677418595
Code barre carton regroup.	50046677418590
Code usine	929000201804
Poids net unitaire	0.224 kg



PHILIPS
sense and simplicity