

# Compact Fluorescent Lamps

PL-C, PL-L, PL-T Lamps

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Generic Designation	Pkg. Qty.	Description	MOL (In.)	Avg. Hrs. Life (230)	Approx. Initial (231) Lumens	Design Lumens (208)	CRI
<b>PL-C Cluster 4-Pin Fluorescent Lamps, Electronic Operation (204)</b>													
13	PL-C	G24q-1	38325-7	\$	PL-C 13W/827/4P/ALTO	CFQ13W/G24q/827	10	2700K	5 3/8	12,000	900	775	82
			38326-5	\$	PL-C 13W/830/4P/ALTO	CFQ13W/G24q/830	10	3000K	5 3/8	12,000	900	775	82
			38327-3	\$	PL-C 13W/835/4P/ALTO	CFQ13W/G24q/835	10	3500K	5 3/8	12,000	900	775	82
			38328-1	\$	PL-C 13W/841/4P/ALTO	CFQ13W/G24q/841	10	4100K	5 3/8	12,000	900	775	82
18	PL-C	G24q-2	38329-9	\$	PL-C 18W/827/4P/ALTO	CFQ18W/G24q/827	10	2700K	5 1/2	12,000	1250	1075	82
			38330-7	\$	PL-C 18W/830/4P/ALTO	CFQ18W/G24q/830	10	3000K	5 1/2	12,000	1250	1075	82
			38332-3	\$	PL-C 18W/835/4P/ALTO	CFQ18W/G24q/835	10	3500K	5 1/2	12,000	1250	1075	82
			38333-1	\$	PL-C 18W/841/4P/ALTO	CFQ18W/G24q/841	10	4100K	5 1/2	12,000	1250	1075	82
26	PL-C	G24q-3	38334-9	\$	PL-C 26W/827/4P/ALTO	CFQ26W/G24q/827	10	2700K	6 1/2	12,000	1800	1550	82
			38335-6	\$	PL-C 26W/830/4P/ALTO	CFQ26W/G24q/830	10	3000K	6 1/2	12,000	1800	1550	82
			38336-4	\$	PL-C 26W/835/4P/ALTO	CFQ26W/G24q/835	10	3500K	6 1/2	12,000	1800	1550	82
			38337-2	\$	PL-C 26W/841/4P/ALTO	CFQ26W/G24q/841	10	4100K	6 1/2	12,000	1800	1550	82
<b>PL-L Long Fluorescent Lamps (204)</b>													
18	PL-L	2G11	34500-9	\$	PL-L 18W/830/4P	FT18W/2G11/830	25	3000K	8 1/8	15,000	1250	1125	82
			35932-3	\$	PL-L 18W/835/4P	FT18W/2G11/835	25	3500K	8 1/8	15,000	1250	1125	82
			34501-7	\$	PL-L 18W/841/4P	FT18W/2G11/841	25	4100K	8 1/8	15,000	1250	1125	82
24	PL-L	2G11	34505-8	\$	PL-L 24W/830/4P	FT24W/2G11/830	25	3000K	12 1/8	15,000	1800	1620	82
			35933-1	\$	PL-L 24W/835/4P	FT24W/2G11/835	25	3500K	12 1/8	15,000	1800	1620	82
			34508-2	\$	PL-L 24W/841/4P	FT24W/2G11/841	25	4100K	12 1/8	15,000	1800	1620	82
36	PL-L	2G11	34511-6	\$	PL-L 36W/830/4P	FT36W/2G11/830	25	3000K	16 3/8	15,000	2900	2610	82
			34942-3	\$	PL-L 36W/835/4P	FT36W/2G11/835	25	3500K	16 3/8	15,000	2900	2610	82
			34513-2	\$	PL-L 36W/841/4P	FT36W/2G11/841	25	4100K	16 3/8	15,000	2900	2610	82
40	PL-L	2G11	30042-6	\$	PL-L 40W/830/4P/RS/IS	FT40W/2G11/RS/830	25	3000K	22 1/2	20,000	3300	2970	82
			30043-4	\$	PL-L 40W/835/4P/RS/IS	FT40W/2G11/RS/835	25	3500K	22 1/2	20,000	3300	2970	82
			30044-2	\$	PL-L 40W/841/4P/RS/IS	FT40W/2G11/RS/841	25	4100K	22 1/2	20,000	3300	2970	82
50	PL-L	2G11	34747-6	\$	PL-L 50W/830/4P/RS	FT50W/2G11/RS/830	25	3000K	22 1/2	20,000	4300	3870	82
			34753-4	\$	PL-L 50W/835/4P/RS	FT50W/2G11/RS/835	25	3500K	22 1/2	20,000	4300	3870	82
			34770-8	\$	PL-L 50W/841/4P/RS	FT50W/2G11/RS/841	25	4100K	22 1/2	20,000	4300	3870	82
55	PL-L	2G11	13844-6	\$	PL-L 55W/950/4P/RS	FT55W/2G11/RS/950	25	5000K	21 3/8	20,000	3650	3358	91
80	PL-L	2G11	38697-9	\$	PL-L 80W/830/4P	FT80W/2G11/830	25	3000K	22 1/2	20,000	6000	5400	82
			38698-7	\$	PL-L 80W/835/4P	FT80W/2G11/835	25	3500K	22 1/2	20,000	6000	5400	82
			38699-5	\$	PL-L 80W/841/4P	FT80W/2G11/841	25	4100K	22 1/2	20,000	6000	5400	82
<b>PL-T Triple 4-Pin Fluorescent Lamps (204)</b>													
18	PL-T	GX24q-2	38437-0	\$	PL-T 18W/827/4P/ALTO	CFTR18W/GX24q/827	12	2700K	4 3/8	12,000	1200	1020	82
			26802-9	\$	PL-T 18W/830/4P/ALTO	CFTR18W/GX24q/830	12	3000K	4 3/8	12,000	1200	1020	82
			26820-1	\$	PL-T 18W/835/4P/ALTO	CFTR18W/GX24q/835	12	3500K	4 3/8	12,000	1200	1020	82
			26822-7	\$	PL-T 18W/841/4P/ALTO	CFTR18W/GX24q/841	12	4100K	4 3/8	12,000	1200	1020	82
26	PL-T	GX24q-3	38440-4	\$	PL-T 26W/827/4P/ALTO	CFTR26W/GX24q/827	12	2700K	5	12,000	1800	1530	82
			26823-5	\$	PL-T 26W/830/4P/ALTO	CFTR26W/GX24q/830	12	3000K	5	12,000	1800	1530	82
			26824-3	\$	PL-T 26W/835/4P/ALTO	CFTR26W/GX24q/835	12	3500K	5	12,000	1800	1530	82
			26825-0	\$	PL-T 26W/841/4P/ALTO	CFTR26W/GX24q/841	12	4100K	5	12,000	1800	1530	82
32	PL-T	GX24q-3	38443-8	\$	PL-T 32W/827/4P/ALTO	CFTR32W/GX24q/827	12	2700K	5 5/8	12,000	2400	2040	82
			26832-6	\$	PL-T 32W/830/4P/ALTO	CFTR32W/GX24q/830	12	3000K	5 5/8	12,000	2400	2040	82
			26833-4	\$	PL-T 32W/835/4P/ALTO	CFTR32W/GX24q/835	12	3500K	5 5/8	12,000	2400	2040	82
			26872-2	\$	PL-T 32W/841/4P/ALTO	CFTR32W/GX24q/841	12	4100K	5 5/8	12,000	2400	2040	82
42	PL-T	GX24q-4	38450-3	\$	PL-T 42W/827/4P/ALTO	CFTR42W/GX24q/827	12	2700K	6 3/8	12,000	3200	2720	82
			26873-0	\$	PL-T 42W/830/4P/ALTO	CFTR42W/GX24q/830	12	3000K	6 3/8	12,000	3200	2720	82
			26875-5	\$	PL-T 42W/835/4P/ALTO	CFTR42W/GX24q/835	12	3500K	6 3/8	12,000	3200	2720	82
			26876-3	\$	PL-T 42W/841/4P/ALTO	CFTR42W/GX24q/841	12	4100K	6 3/8	12,000	3200	2720	82
			13487-4	X \$ (242)	PL-T 42W/830/4P/HTA ALTO	CFTR42W/GX24q/830	12	3000K	6 3/8	12,000	3200	2720	82
			13488-2	X \$ (242)	PL-T 42W/835/4P/HTA ALTO	CFTR42W/GX24q/835	12	3500K	6 3/8	12,000	3200	2720	82
			13659-8	X \$ (242)	PL-T 42W/841/4P/HTA ALTO	CFTR42W/GX24q/841	12	4100K	6 3/8	12,000	3200	2720	82
57	PL-T	GX24q-5	14631-6	\$	PL-T 57W/830/4P/A	CFTR57W/GX24q/830	10	3000K	7 5/8	12,000	4300	3741	82
			14632-4	\$	PL-T 57W/835/4P/A	CFTR57W/GX24q/835	10	3500K	7 5/8	12,000	4300	3741	82
			14633-2	\$	PL-T 57W/841/4P/A	CFTR57W/GX24q/841	10	4100K	7 5/8	12,000	4300	3741	82

**NEW!**

X Orders will be shipped until inventory is depleted; no longer manufactured  
 For the most current product information, go to the e-catalog on [www.philips.com](http://www.philips.com)  
 Compact Fluorescent symbols and footnotes located on page 87  
 □ This product utilizes ALTO® Lamp Technology