

# Compact Fluorescent Lamps

PL-H®, PL-S, PL-C Lamps

| Watts                                     | Bulb | Base | Old Product Number | Old Symbols, Footnotes | New Product Number | New Ordering Code         | Generic Designation | Pkg. Qty. | Description | MOL (In.) | Avg. Hrs. Life (230) | Approx. Initial (231) Lumens | Design Lumens (208) | CRI |
|---|------|------|--------------------|------------------------|--------------------|---------------------------|---------------------|-----------|-------------|-----------|----------------------|------------------------------|---------------------|-----|
| <b>PL-S Short Fluorescent Lamps (204)</b> |      |      |                    |                        |                    |                           |                     |           |             |           |                      |                              |                     |     |
| 5   | PL-S | G23  | 33233-8            | X                      | \$ 14671-2         | PL-S 5W/827/2P/ALTO       | CFT5W/G23/827       | 10        | 2700K       | 4 ½       | 10,000               | 250                          | 210                 | 82  |
|   |      |      | <b>NEW!</b>        |                        | \$ 14868-4         | PL-S 5W/841/2P/ALTO       | CFT5W/G23/842       | 10        | 4100K       | 4 ½       | 10,000               | 250                          | 210                 | 82  |
| 7   | PL-S | G23  | 34256-8            | X                      | \$ 14871-8         | PL-S 7W/827/2P/ALTO       | CFT7W/G23/827       | 10        | 2700K       | 5 ½       | 10,000               | 400                          | 360                 | 82  |
|   |      |      | 32780-9            | X                      | \$ 14872-6         | PL-S 7W/835/2P/ALTO       | CFT7W/G23/835       | 10        | 3500K       | 5 ½       | 10,000               | 400                          | 360                 | 82  |
|   |      |      | 33869-9            | X                      | \$ 14873-4         | PL-S 7W/841/2P/ALTO       | CFT7W/G23/841       | 10        | 4100K       | 5 ½       | 10,000               | 400                          | 360                 | 82  |
|   |      |      | 33384-9            | X                      | \$ 14874-2         | PL-S 7W/850/2P/ALTO       | CFT7W/G23/850       | 10        | 5000K       | 5 ½       | 10,000               | 380                          | 340                 | 82  |
| 9   | PL-S | G23  | 34257-6            | X                      | \$ 14867-6         | PL-S 9W/827/2P/ALTO       | CFT9W/G23/827       | 10        | 2700K       | 6 ¾       | 10,000               | 600                          | 540                 | 82  |
|   |      |      | 32786-6            | X                      | \$ 14869-2         | PL-S 9W/835/2P/ALTO       | CFT9W/G23/835       | 10        | 3500K       | 6 ¾       | 10,000               | 600                          | 540                 | 82  |
|   |      |      | 33870-7            | X                      | \$ 14870-0         | PL-S 9W/841/2P/ALTO       | CFT9W/G23/841       | 10        | 4100K       | 6 ¾       | 10,000               | 600                          | 540                 | 82  |
|   |      |      | 33385-6            | X                      | \$ 14680-3         | PL-S 9W/850/2P/ALTO       | CFT9W/G23/850       | 10        | 5000K       | 6 ¾       | 10,000               | 570                          | 510                 | 82  |
| 13  | PL-S | GX23 | 26219-6            | X                      | \$ 14681-1         | PL-S 13W/827/2P/ALTO      | CFT13W/GX23/827     | 10        | 2700K       | 7 ¼       | 10,000               | 825                          | 740                 | 82  |
|   |      |      | 26212-1            | X                      | \$ 14682-9         | PL-S 13W/827/2P/ALTO/BULK | CFT13W/GX23/827     | 50        | 2700K       | 7 ¼       | 10,000               | 825                          | 740                 | 82  |
|   |      |      | 26202-2            | X                      | \$ 14683-7         | PL-S 13W/830/2P/ALTO      | CFT13W/GX23/830     | 10        | 3000K       | 7 ¼       | 10,000               | 825                          | 740                 | 82  |
|   |      |      | 26214-7            | X                      | \$ 14684-5         | PL-S 13W/835/2P/ALTO      | CFT13W/GX23/835     | 10        | 3500K       | 7 ¼       | 10,000               | 825                          | 740                 | 82  |
|   |      |      | 26213-9            | X                      | \$ 14685-2         | PL-S 13W/841/2P/ALTO      | CFT13W/GX23/841     | 10        | 4100K       | 7 ¼       | 10,000               | 825                          | 740                 | 82  |
|   |      |      | 26229-5            | X                      | \$ 14686-0         | PL-S 13W/841/2P/ALTO/BULK | CFT13W/GX23/841     | 50        | 4100K       | 7 ¼       | 10,000               | 825                          | 740                 | 82  |
|   |      |      | 26216-2            | X                      | \$ 14687-8         | PL-S 13W/850/2P/ALTO      | CFT13W/GX23/850     | 10        | 5000K       | 7 ¼       | 10,000               | 800                          | 720                 | 82  |
|   |      |      | 14308-1            | X                      | \$ 14688-6         | PL-S 13W/850/2P/ALTO/BULK | CFT13W/GX23/850     | 50        | 5000K       | 7 ¼       | 10,000               | 800                          | 720                 | 82  |

**NEW!**

| Watts                                     | Bulb | Base  | Product Number | Symbols, Footnotes | Ordering Code         | Generic Designation | Pkg. Qty. | Description | MOL (In.) | Avg. Hrs. Life (230) | Approx. Initial (231) Lumens | Design Lumens (208) | CRI |
|---|------|-------|----------------|--------------------|-----------------------|---------------------|-----------|-------------|-----------|----------------------|------------------------------|---------------------|-----|
| <b>PL-H® High Fluorescent Lamps (204)</b> |      |       |                |                    |                       |                     |           |             |           |                      |                              |                     |     |
| 60  | PL-H | 2G8-1 | 13368-6        | \$                 | PL-H 60W/830/4P/ALTO  | TBD                 | 10        | 3000K       | 7 ¼       | 20,000               | 4000                         | 3440                | 82  |
|   |      |       | 13369-4        | \$                 | PL-H 60W/841/4P/ALTO  | TBD                 | 10        | 4100K       | 7 ¼       | 20,000               | 4000                         | 3440                | 82  |
| 85  | PL-H | 2G8-1 | 13370-2        | \$                 | PL-H 85W/830/4P/ALTO  | TBD                 | 10        | 3000K       | 8 ¾       | 20,000               | 6000                         | 5160                | 82  |
|   |      |       | 13371-0        | \$                 | PL-H 85W/841/4P/ALTO  | TBD                 | 10        | 4100K       | 8 ¾       | 20,000               | 6000                         | 5160                | 82  |
| 120                                       | PL-H | 2G8-1 | 13372-8        | \$                 | PL-H 120W/830/4P/ALTO | TBD                 | 10        | 3000K       | 11 ¾      | 20,000               | 9000                         | 7740                | 82  |
|   |      |       | 13373-6        | \$                 | PL-H 120W/841/4P/ALTO | TBD                 | 10        | 4100K       | 11 ¾      | 20,000               | 9000                         | 7740                | 82  |

|   |      |                   |                 |      |                       |                 |        |                   |                 |        |       |      |        |      |      |    |
|---|------|-------------------|-----------------|------|-----------------------|-----------------|--------|-------------------|-----------------|--------|-------|------|--------|------|------|----|
| <b>PL-C Cluster 2-Pin Fluorescent Lamps (204)</b> |      |                   |                 |      |                       |                 |        |                   |                 |        |       |      |        |      |      |    |
| 13  | PL-C | GX23-2            | 38310-9         | \$   | PL-C 13W/827/USA/ALTO | CFQ13W/GX23/827 | 10     | 2700K             | 4 ¾             | 10,000 | 860   | 735  | 82     |      |      |    |
|   |      |                   | 38311-7         | \$   | PL-C 13W/830/USA/ALTO | CFQ13W/GX23/830 | 10     | 3000K             | 4 ¾             | 10,000 | 860   | 735  | 82     |      |      |    |
|   |      |                   | 38312-5         | \$   | PL-C 13W/835/USA/ALTO | CFQ13W/GX23/835 | 10     | 3500K             | 4 ¾             | 10,000 | 860   | 735  | 82     |      |      |    |
|   |      |                   | 38313-3         | \$   | PL-C 13W/841/USA/ALTO | CFQ13W/GX23/841 | 10     | 4100K             | 4 ¾             | 10,000 | 860   | 735  | 82     |      |      |    |
|   |      |                   | 38314-1         | \$   | PL-C 13W/827/ALTO     | CFQ13W/G24d/827 | 10     | 2700K             | 5 ½             | 10,000 | 900   | 770  | 82     |      |      |    |
| 18  | PL-C | G24d-1            | 38315-8         | \$   | PL-C 13W/830/ALTO     | CFQ13W/G24d/830 | 10     | 3000K             | 5 ½             | 10,000 | 900   | 770  | 82     |      |      |    |
|   |      |                   | 18              | PL-C | G24d-2                | 38316-6         | \$     | PL-C 18W/827/ALTO | CFQ18W/G24d/827 | 10     | 2700K | 6    | 10,000 | 1250 | 1070 | 82 |
|   |      |                   |                 |      |                       | 38317-4         | \$     | PL-C 18W/830/ALTO | CFQ18W/G24d/830 | 10     | 3000K | 6    | 10,000 | 1250 | 1070 | 82 |
|   |      |                   |                 |      |                       | 38318-2         | \$     | PL-C 18W/835/ALTO | CFQ18W/G24d/835 | 10     | 3500K | 6    | 10,000 | 1250 | 1070 | 82 |
| 38319-0   | \$   | PL-C 18W/841/ALTO | CFQ18W/G24d/841 | 10   | 4100K                 | 6               | 10,000 | 1250              | 1070            | 82     |       |      |        |      |      |    |
| 26  | PL-C | G24d-3            | 38321-6         | \$   | PL-C 26W/827/ALTO     | CFQ26W/G24d/827 | 10     | 2700K             | 6 ¾             | 10,000 | 1800  | 1545 | 82     |      |      |    |
|   |      |                   | 38322-4         | \$   | PL-C 26W/830/ALTO     | CFQ26W/G24d/830 | 10     | 3000K             | 6 ¾             | 10,000 | 1800  | 1545 | 82     |      |      |    |
|   |      |                   | 38323-2         | \$   | PL-C 26W/835/ALTO     | CFQ26W/G24d/835 | 10     | 3500K             | 6 ¾             | 10,000 | 1800  | 1545 | 82     |      |      |    |
|   |      |                   | 38324-0         | \$   | PL-C 26W/841/ALTO     | CFQ26W/G24d/841 | 10     | 4100K             | 6 ¾             | 10,000 | 1800  | 1545 | 82     |      |      |    |

|  |      |         |         |    |                   |                  |    |       |     |        |      |      |    |
|--|------|---------|---------|----|-------------------|------------------|----|-------|-----|--------|------|------|----|
| <b>PL-C Cluster 2-Pin Fluorescent Lamps, 15mm Tube Diameter (204, 222)</b> |      |         |         |    |                   |                  |    |       |     |        |      |      |    |
| 20   | PL-C | GX32d-2 | 20478-4 | \$ | PL-C 15mm/22W/827 | CFQ20W/GX32d/827 | 40 | 2700K | 6   | 10,000 | 1200 | 995  | 82 |
| 27   | PL-C | GX32d-3 | 20479-2 | \$ | PL-C 15mm/28W/827 | CFQ27W/GX32d/827 | 40 | 2700K | 6 ¾ | 10,000 | 1600 | 1325 | 82 |

X Orders will be shipped until inventory is depleted; no longer manufactured; new product features ALTO® Lamp Technology.

For the most current product information, go to the e-catalog on [www.philips.com](http://www.philips.com)

Compact Fluorescent symbols and footnotes located on page 87

□ This product utilizes ALTO® Lamp Technology