

Phone, Modem and DSL Surge Protective Devices



A.

A. IG2TM

- Protects 2 lines
- Type 1 enclosure
- Tip-To-Ground, Tip-To-Ring and Ring-To-Ground Modes
- 40 kA surge protection per line
- #24 to #16 gauge AWG
- Gas tube protection 350 VDC breakdown
- UL497A



B.

B. IG4TM

- Protects 4 lines
- Type 1 enclosure
- Tip-To-Ground, Tip-To-Ring and Ring-To-Ground Modes
- 40 kA surge protection per line
- #24 to #16 gauge AWG
- Gas tube protection 350 VDC breakdown
- UL497A



C.

C. IG2T3R

- Protects 2 lines (expandable to 12 Lines)
- Type 3R rainproof enclosure
- Tip-To-Ground, Tip-To-Ring and Ring-To-Ground Modes
- 40 kA surge protection per line
- #24 to #16 gauge AWG
- Gas tube protection 350 VDC breakdown
- UL497A

Model #	Lines	Wire Configuration	Location
A. IG2TM	2	4	Indoor
B. IG4TM	4	8	Indoor
C. IG2T3R	2 (up to 12)	4 (up to 24 wire)	Indoor/Outdoor