

EJ600 Series 24-Hour or 7-Day In-Wall Timers



- Up to 14 (7 ON/OFF) programmable events per day
- Random setting turns lights ON/OFF at different times so it appears someone is always at their home or business
- Auto Daylight Saving Time adjustment
- Incandescent/Fluorescent/CFL/LED compatible
- Astronomic feature auto adjusts to sunrise/sunset
- Can be used for 24-Hour or 7-Day load control of lights, fans, pumps and other medium-duty loads
- Built-in rechargeable lithium ion battery backup
- Single-pole or 3-way compatible
- For use with decorator-style wall plate (not included)
- Requires neutral wire

Model #	Color
C. EJ600	White
D. EJ600A	Almond

Ratings:	
Input Voltage: 120 VAC, 60 Hz.	Inductive Ballast: 500 VA
General Purpose: 12 A, 120 VAC, 60 Hz.	Motor: 1/2 HP
Resistive (heater): 12 A, 120 VAC, 60 Hz.	Operating Temperature: 32°F to 104°F (0°C to 40°C)
Tungsten (incandescent): 15 A single-gang, 12 A multi-gang	Warranty: Limited 1 year



C.

D.



E.



F.

EJ351 Programmable 24-Hour Security Timer



- Up to 48 ON/OFF programmable events
- No neutral required
- Self learning, adapts to your schedule to meet your demands
- Random setting turns lights ON/OFF at different times so it appears someone is always at their home or business
- Controls incandescent lighting
- 15-minute memory guard protects against power failure
- For use with standard or decorator-style wall plate (not included)

Ratings:
Input Voltage: 120 VAC, 60 Hz.
Min. Wattage: 40 W
Max. Wattage: 500 W Incandescent
Inductive Ballast: 4 A
Operating Temperature: 32°F to 104°F (0°C to 40°C)
Warranty: Limited 1 year

Model #	Color
E. EJ351	White

Not for use with CFL/LED bulb

EJ500 Electronic In-Wall Switch Timer



- Versatile 7-Day scheduling
- Up to 14 (7 ON/OFF) programmable events per day
- No neutral required
- Random setting turns lights ON/OFF at different times so it appears someone is always at their home or business
- Auto Daylight Saving Time adjustment
- Astronomic feature auto adjusts to sunrise/sunset
- Controls incandescent lighting
- Battery backup
- Single-pole or 3-way compatible
- For use with decorator-style wall plate (not included)

Ratings:	Tungsten: 4 A
Input Voltage: 120 VAC, 60 Hz.	Inductive Ballast: 4 A
Min. Wattage: 40 W	Operating Temperature: 32°F to 104°F (0°C to 40°C)
Max. Wattage: 500 W Incandescent	Warranty: Limited 1 year

Model #	Color
F. EJ500	White

Not for use with CFL/LED bulbs