






	Description	Part Number	Master Carton Qty	Suggested Trade
	Includes shrouds and soffit mount Accepts Par, PL, Fluorescent, R, or Quartz lamps, 150 watts 120 Volts AC FL300B Dual Floodlight - Black * FL300W Dual Floodlight - White *	61811 61801	3 3	83.00 83.00
	Ultra Eye Lens with 2 motion sensors Includes shrouds and bulb Rain tight enclosure, UL rated IP54 120 Volts AC HS150B 150 Watt Halogen Sensor Light - Black ** HS150W 150 Watt Halogen Sensor Light - White **	63301 63311	3 3	83.00 83.00
	Ultra Eye Lens with 2 motion sensors Includes shrouds and bulb Rain tight enclosure, UL rated IP54 120 Volts AC HS300B 300 Watt Halogen Sensor Light - Black HS300W 300 Watt Halogen Sensor Light - White	63321 63331	3 3	94.00 94.00
	Wall and ceiling mount IR motion detector Full circular 360° coverage, 40' Range Switching capacity 0 - 600 watts 120 Volts AC IS360B Motion Sensor Switch - Black IS360W Motion Sensor Switch - White	60251 60261	6 6	107.00 107.00
	Switching Capacity 0 to 600 Watts No minimum load requirement Use with existing lights 120 Volts AC IS140B Motion Sensor Switch - Black IS140W Motion Sensor Switch - White	60291 60301	3 3	81.00 81.00

* Energy Star Qualified when used in night lux setting with maximum of 100 watt bulbs.

** Energy Star qualified when used in night lux setting.