


TT 175

Gas Torches



TT 175 Specifications

Item No.	71175
Temperature	2400°F (1316°C)
Fuel Capacity	60 ml refillable fuel tank
Operating Time	Up to 120 min. continuous use (on mid setting)
Fuel Type	Standard butane fuel triple filtered
Ignition	Water proof piezo electronic system
Nozzle Diameter	0.8" (19.8 mm)
Net Weight	0.6 lb (9.4 oz)
Dimensions	5.3" x 4.0" x 1.5" (l x w x d)
Single Sell Pack	dimensions: 7.4" x 5.5" x 1.8" weight: 0.8 lbs (12.5 oz)
Warranty	one year limited
Certifications	CE, RoHs Compliant

ThermaTorch™ 175

ThermaTorch™ 175 has adjustable airflow and flame control. It incorporates a high capacity 60ml refillable fuel tank for up to 120 minutes of continuous use.

Applications

For caramelizing creme brulee, plumbing, brazing, prosthetics, soldering and desoldering

Key Features:

- Quality design
- Durable construction
- Safety kill switch
- Removable base



Triple Filtered Butane

BT 01 - 1 oz (28.4gm) No. 70001

BT 05 - 5 oz (142gm) No. 70005



Caramelize Creme Brulee



Plumbing



Braze



Prosthetics



Solder and Desolder



www.steinel.net