









## Stylmaster 'C' Incandescent Fixtures: Mounting Hoods and Cast Outlet Boxes

Suitable for use in Wet Locations.  
Aluminum Mounting Hoods and Outlet Boxes.

	<b>Size (Inches)</b>	<b>Catalogue Number Copper-Free Aluminum</b>
	<b>Pendant</b> Furnished with setscrew, 3/4" to 1/2" reducer for 1/2" stem, medium base socket	<b>VCA75</b>
	<b>Ceiling - with Junction Box</b> With five tapped openings and three close-up plugs.  3/4"	<b>VCX75</b>
	<b>Ceiling - for Outlet Box</b> Fits SEH or VCJB cast outlet box or 3-1/4" or 4" octagonal outlet box. With screws and gasket.	<b>VCOB1</b>
	<b>45° Stanchion</b>  1-1/4"	<b>VCAN125</b>
	<b>Wall - with Junction Box*</b> With five tapped openings and three close-up plugs.  3/4"	<b>VCWB75</b>
	<b>Wall - for Outlet Box*</b> Fits SEH or VCJB cast outlet box or 3-1/4" or 4" octagonal outlet box. With screws and gasket.	<b>VCOBW1</b>
	<b>Wall - Side Hubs</b> With two side hubs and one close-up plug.  3/4"	<b>VCW75</b>
	<b>Cast Outlet Box Only - Five Tapped Openings</b> Four close-up plugs. No socket. Fits VCOB, VCOBW, and VCWB.  1/2" 3/4"	<b>VCJB50 VCJB75</b>

\* Use 30° angle reflectors for wall installations — centre line of fixture must be located at least 5-3/4" away from wall. For shallow or standard dome — consult factory.

## Stylmaster 'C' Enclosed and Gasketed Incandescent Lighting Fixtures

Attractively Styled Economical Fixture with Prismatic Globe. UNILETS® for Use with Threaded Metal Conduit.

### Applications

- Enclosed and gasketed lighting fixtures for use in storage areas, tunnels, subways, chemical plants and other areas where moisture, dirt or corrosive atmospheres are a problem.
- Suitable for use in wet locations.
- Standard fixtures designed for 60- to 300-watt medium base incandescent lamps.
- Pendant, ceiling, stanchion and wall mount.
- Fiberglass reinforced polyester reflectors for installations where fixture is subject to severe corrosive conditions or vandalism.

### Features

- Modern styling, with clean-line mounting hood and prismatic glass globe, plus optional guard.
- Prismatic globe, furnished as standard, eliminates glare and distributes light evenly. See "Options" for other globes available.
- Globe seats firmly against composition gasket in mounting hood to keep out dirt and moisture. Full threads eliminate "cross threading".
- Fixture is complete with gaskets and socket. Socket is easily removed for wiring.
- Porcelain socket construction assures long trouble-free operation in high ambient installations.
- Polyester reflectors are secured to mounting hoods with screws (furnished).
- Guards are threaded for fast servicing.
- Fiberglass reinforced polyester reflector in standard dome and 30° angle.

### Standard Materials

- *Mounting hoods:* copper-free aluminum.
- *Guards:* cast copper-free aluminum.
- *Reflectors:* fiberglass reinforced polyester.
- *Socket:* porcelain with copper alloy screw shell.
- *Globes:* prismatic glass. See "Options" for other types available.



## Stylmaster 'C' Enclosed and Gasketed Incandescent Lighting Fixtures

Attractively Styled Economical Fixture with Prismatic Globe. UNILETS® for Use with Threaded Metal Conduit.

### Standard Finishes

- *Mounting hoods:* baked gray epoxy.
- *Aluminum guards:* baked gray epoxy.
- *Steel reflectors:* baked white porcelain enamel.
- *Fiberglass reinforced polyester reflectors:* natural finish.
- *Socket and globes:* natural finish.

### Options

- To order fixture with other than standard clear glass globe, add suffix letters to catalogue number as indicated in table, and adjust difference in price.

Colour	Glass Globe	Plastic Globe
Amber	-AM	-PAM
Blue	-BL	—
Green	-GR	-PGR
Red	-RE	-PRE
Clear Heat-Resistant	-HR	—

- To order fixture complete with reflector, add suffix letters to catalogue number as indicated in table and adjust difference in price.

Reflector	Polyester
Standard	-PST
Shallow	—
Angle	-PAN

- To order fixture c/w clear globe and 48 LED beacon style light source, use the following suffixes:

- LA** - Amber LED
- LB** - Blue LED
- LG** - Green LED
- LH** - High Intensity Red LED
- LR** - Red LED

### Compliances

- CSA approved. LR25428
- Class I, Div. 2, Groups A, B, C, D
- Class II, Div. 1 & 2, Groups E, F, G
- Class III
- CSA Enclosure 4x



### Mounting Hood

Pendant style shown has setscrew to prevent fixture stem from turning. Other styles include stanchion, ceiling and wall mounting.



### Socket

Porcelain socket mounted to an inner reflector for higher light output.



### Globe

Attractive, tapered prismatic glass globes for glare elimination and uniform light distribution. Colours available—also vandal-resistant plastic globes. Globe seats firmly against gasket to exclude moisture, dirt and vapours.

### Guard

Fully threaded - Eliminates cross threading.