

McGILL® String-O-Lights

Low Cost Temporary Lighting

Applications

- McGill offers a variety of temporary job site lighting systems, from reusable, low cost cable versions to an assortment of open conductor styles.

Features

- They are available in 50' to 200'/15.2 to 61 meters lengths of 2- and 3-conductor and 12 and 14 gauge wire with 5 to 10 cage/socket assemblies.
- Brass sockets are enclosed in weather-resistant molded PVC, and plastic connectors provide greater reliability.
- Packaging provides tangle-free, on-the-job handling and installation.
- Easy-open cages snap open and closed for faster installation without tools and easy lamp replacements.
- Non-corrosive cages are fastened to sockets by a non-corrosive collar and accommodate up to 200 Watt bulbs.
- Cable styles meet 2008 NEC requirements.
- Convenient, economical temporary lighting.
- 110'/30.5 m messenger wire available to support string where needed.
- Fully assembled; ready for installation.
- Weather-resistant sockets.
- All parts sold separately.

Standard Materials

- Cages: yellow plastic

Certification and Compliance

- Molded Cable Version
 - UL Listed: E88103
 - UL Standard: 1088
 - Meets OSHA requirements
 - CSA Certified: LL89639 ¹
 - CSA Standard: C22.2 No. 12



Flat Wire Cable Style




OPEN CONDUCTOR

Illustrated Features




Easy-Open Cages



FLATWIRE



Packaging



MOLDED CABLE

LIGHTING: MCGILL TEMPORARY

Lighting

	Length Ft/M	No. of Cages/ Sockets	Socket Spacing Ft/M	Catalog Numbers	
				for A-23 Bulb	for PS-30 Bulb
Molded Cable Styles – UL Listed					
12/2-SJTW cable with plug/boot on one end and connector/cap on other end	100/30.5	10	10/3.0	2252-0018	—
12/2-SJTW cable	100/30.5	10	10/3.0	2252-0019	—
12/2-STW extra hard usage cable with weather protected plug/boot	100/30.5	10	10/3.0	2252-5007 ¹	—
12/3-SJTW cable with 5-15 plug/boot on one end and connector/cap on other end	100/30.5	10	10/3.0	2252-0026	—
12/3-SJTW cable	100/30.5	10	10/3.0	2252-0027	—
14/2-SJTW cable	100/30.5	10	10/3.0	2252-0007	2252-0009
14/2-SJTW cable with plug/protective rubber boot on one end	100/30.5	10	10/3.0	2252-0012	2252-0013
14/2-SJTW cable	50/15.2	5	10/3.0	2252-0031 *	—
14/3-SJTW cable	100/30.5	10	10/3.0	2252-0014	2252-0015
14/3-SJTW cable with 5-15 plug/boot on one end and connector/cap on other end	100/30.5	10	10/3.0	2252-0024	2252-0025
14/3-SJTW cable	50/15.2	5	10/3.0	2252-0034 *	—

* Contact Technical Service for UL data

¹ CSA Certification only.