

5000 Series Industrial Extension Lights

Thermoplastic Handle With or Without Receptacle

Features

- Industrial-duty extension lights resist impact, abrasion and oil.
- Yellow handles with receptacle, yellow cords, and grounded cages enhance safety, while easy-open cages speed relamping.
- All-weather cords have molded plugs for durability.
- Cages feature rotating hooks and NO-ROL design for accurate light positioning.
- Accommodates up to 200 Watt rough service bulbs.
- Meets NEC requirements for power tool grounding.
- 13 Amp, 125 Vac receptacle rating.
- Long-life Levolver™ switch mechanism in handle with protective thumb guard.


Standard Materials

- Cords: 16/3-SJTW thermoplastic
- Cages: 10 gauge steel



Standard Finish

- Cages: zinc plated, chrome finish

Options

- 15 Amp, 120 Volt CSA Certified versions available. Items available in a CSA version will be marked with a . Add the prefix **C** to the beginning of the catalog number.

Certifications and Compliances

- UL Listed (with cord): E59071
- UL Listed (without cord): E59054
- UL Standard: 153
- Meets OSHA requirements
- CSA Certified (with cord): LL89639 
- CSA Certified (without cord): LL56247 
- CSA Standard: C22.2 No. 12



5000-SRG




5000-SRG, easy open cage



5025-SRG

 100 Watt Maximum for UL Listing and CSA Certification.

 CSA Certification only.

5000 Series Industrial Extension Lights

Thermoplastic Handle With or Without Receptacle

	Catalog Numbers			
	with out Cord	with 1' / 0.3m 16/3-SJTW Cord	with 25' / 7.6m 16/3-SJTW Cord	with 50' / 15.2m 16/3-SJTW Cord
Closed-End Extension Lights				
Handle and cage	5000-G	—	5025-G	5050-G
Handle and cage	C5000-G ^{CSA}	—	C5025-G ^{CSA}	C5050-G ^{CSA}
Handle and cage with reflector	5000-RG	—	5025-RG	5050-RG
Handle and cage with reflector	C5000-RG ^{CSA}	—	C5025-RG ^{CSA}	C5050-RG ^{CSA}
Handle and cage with switch	5000-SG	—	5025-SG	5050-SG
Handle and cage with switch	C5000-SG ^{CSA}	—	C5025-SG ^{CSA}	C5050-SG ^{CSA}
Handle and cage with switch and reflector	5000-SRG	5012-SRG ^{100W}	5025-SRG	5050-SRG
Handle and cage with switch and reflector	C5000-SRG ^{CSA}	C5012-SRG ^{100W CSA}	C5025-SRG ^{CSA}	C5050-SRG ^{CSA}
Handle and cage with switch and reflector and GFCI	—	—	5025-SRG-GFCI	—
Handle and cage, no receptacle	5000-GN	—	5025-GN	5050-GN
Handle and cage, no receptacle	C5000-GN ^{CSA}	—	C5025-GN ^{CSA}	C5050-GN ^{CSA}
Handle and cage with reflector, no receptacle	5000-RGN	—	5025-RGN	5050-RGN
Handle and cage with reflector, no receptacle	C5000-RGN ^{CSA}	—	C5025-RGN ^{CSA}	C5050-RGN ^{CSA}
Handle and cage with switch, no receptacle	5000-SGN	—	5025-SGN	5050-SGN
Handle and cage with switch, no receptacle	C5000-SGN ^{CSA}	—	C5025-SGN ^{CSA}	C5050-SGN ^{CSA}
Handle and cage with switch and reflector, no receptacle	5000-SRGN	—	5025-SRGN	5050-SRGN
Handle and cage with switch and reflector, no receptacle	C5000-SRGN ^{CSA}	—	C5025-SRGN ^{CSA}	C5050-SRGN ^{CSA}
Handle and non-metallic cage	—	—	5999-GH	—
Handle and non-metallic cage	—	—	C5999-GH ^{CSA}	—
Handle and non-metallic cage with reflector	—	—	5999-RGH	—
Handle and non-metallic cage with reflector	—	—	C5999-RGH ^{CSA}	—
Handle and non-metallic cage with switch	—	—	5999-SGH	—
Handle and non-metallic cage with switch	—	—	C5999-SGH ^{CSA}	—
Handle and non-metallic cage with switch and reflector	—	—	5999-SRGH	—
Handle and non-metallic cage with switch and reflector	—	—	C5999-SRGH ^{CSA}	—
Replacement Cord Sets				
Cord set with molded plugs			6229-1	6229-2
			Catalog Number	
			With Out Reflector	With Reflector
Cages				
Wire cage			8171	8170
Vinyl insulated metal cage (100 Watt A-21)			08171	08170
Non-metallic cage (100 Watt A-19)			—	8224
			Catalog Number	
			With Out Switch	With Switch
Handles and Sockets				
Handle and socket for 5000			0877	0865
Handle and socket for 5000-N			0877-N	0865-N
Socket for 5000 and 5000-N			00868	868

^{100W} 100 Watt Maximum for UL Listing and CSA Certification.
^{CSA} CSA Certification only.