

## UNILITE. The universal 360° lighting solution

The versatile rotating head puts light where it's needed. Lay the UNILITE down and twist the light head to point at your work. Clip it to a pocket, safety harness, turnout or belt with its heavy duty nylon clip. For straight on illumination the right angle section can be removed. A stainless split ring and snap are included for attachment to clothing loops and button holes.



- Prefocused high intensity xenon lamp.
- Head rotates 360° to direct beam in any direction
- Split ring and clip included for attachment to coat pocket, belt or strap
- Shock absorbing rubber lens cover
- Continuous or momentary thumb switch
- Tough, non-corroding ABS and polycarbonate plastic
- Waterproof to 10 feet
- Ratings: UL Listed Class I Div 2.



Also Available As eLED



UniLite is also available with exclusive UK Projection Optics ZOOM lamp module

## 2AA/4AA Accessories

### Universal Helmet Clip

- Swivels to any position for perfect alignment
- Tough nylon construction will not break
- Fits any hard hat, fire helmet, ear muffs, bump caps, or helmets without brim



Product # 14819



### Stainless Steel Adjustable Fire Helmet Clip

- Clips to helmet rim
- Adjustable, swivels to any position for perfect alignment

Product # 14818



### Stainless Steel Fixed Helmet Clip

- Clips to helmet rim
- Fixed position for stability

Product # 14802



### Rylee Fire Helmet Clip

- Stainless steel
- Clips to helmet brim with protective clamp which prevents damage to brim

Product # 14851



### 2AA/4AA Safety Wand

- Light weight solution for directing traffic
- 7.5 inch profile

Product # 14808



### 2AA & 4AA Nylon Belt Pouches

- Made of durable nylon with Velcro® closure
- Small, compact design allows convenient transport of UK 4AA light

Product # 14816 - 4AA

Product # 15803 - 2AA



### 2AA/4AA BIANCHI Holster

- BINACHI AccuMold® forming
- Fits 4AA, 2AA, 2L

Basket weave simulated leather

Product # 14832

Smooth simulated leather

Product # 14833

Ballistic Nylon

Product # 14834





# MINI-LIGHT SERIES



O-ring sealed against mud and water. Case is non-conductive and will not corrode.



Hat clip and key ring included.. eLED modls include rubber lens cover



Also Available As eLED



Night vision protecting red LED accessory lamp available for both Mini Pocket Light and 2AAA Penlight



## UK2AAA Mini Pocket Light. Brightest 2AAA in its class

This waterproof mini-light with compact parallel battery loading clips to hat or safety glasses for hands free lighting while doing repairs, maintenance or walking in the dark. Rated brightest 2AAA light (xenon model) in its class by Aviation Consumer Magazine.

- Available with high intensity 1.13 watt Xenon or white eLED lamp (optional accessory red LED also available)
- Powered by 2 AAA alkaline cells
- Compact size (.74 x 2.9 x 1.1 inch)
- ABS and Lexan® construction
- Ratings: UL Listed Class I Div 2 (xenon only)

See Technical Specifications On Page 15



O-ring sealed against mud and water and will not corrode when wet



Penlight S model includes momentary or continuous click switch for easy one-hand operation



## UK2AAA Penlight. Puts out more illumination than lights three times its size

Wet or dry, this penlight's non-conductive high impact case allows use around circuitry or electricity. Rated brightest 2AAA light in its class by Aviation Consumer.

- Available with high intensity 1.13 watt Xenon or white eLED lamp (optional accessory red LED also available)
- Powered by 2 AAA alkaline cells
- Compact fingertip size (.74 dia. x 4.8 inch)
- Tough Lexan® construction
- Ratings: UL Listed Class I Div 2 (xenon only)

Flexible fiberoptic inspection wand

**Reach For It...It's Ready.**  
**4AA Series NiMH Rechargeable Lights**  
**Give You Freedom From Batteries!**



**RAPID** Recharge  
In Just 90 Minutes

*1.5 hour fast charger mounts  
to wall or counter top;  
allows 100-240 VAC 50-60 Hz  
or 12 VDC auto input*



**Why Rechargeable?**

You depend on your lights to be ready at a moments notice. UK Rechargeable technology keeps your lights ready just like a cell phone. Consider these additional benefits...

**Economics**

Just add up the cost of all those disposable alkaline batteries and compare to the cost-efficiency of rechargeables.

**Convenience**

Always ready. Always full brightness.

**Versatility**

UK Rechargeable technology is available for the entire 4AA family including the UniLite and eLED or Xenon lamps.

**Brightness**

Get more lumens from rechargeables than with alkaline-cell power.

**UK C4/C8 NiCad Pak.**



**UPGRADE** To Rechargeable  
Or Switch Between  
Alkaline & NiMH C-Cells





# HAND LIGHTS



Molded rubber glare reducing bezel cover

O-ring sealed against dust, water and mud

Attaches with unbreakable nylon clip, lanyard or stainless steel ring



## UK 300. Built for harsh environments

The UK 300 combines state-of-the-art safety features with a dazzling high intensity smoke cutting beam. A must for confined space workers, search & rescue professionals, safety personnel and firefighters. Passes UL 30 feet drop test to concrete.

- Bright 3.6 watt Xenon beam powered by 3 alkaline C-cells
- Waterproof, non-corroding and shock resistant construction make this light handle any environment
- Patented, polarized battery holder and hydrogen vent minimize explosive damage and leaky batteries
- Durable construction of ABS, polycarbonate, nylon, PP rubber
- Size: 8.7 x 2.46 x 1.7 inch
- Ratings: UL, FM, CSA Listed Class I Div 2

See Technical Specifications On Page 15

## Sunlight SL4 & SL6. Brighter than lights twice their length

Unique side-by-side battery configuration still allow these 4 or 6 C-cell lights to easily fit in a coat pocket. Emits narrow and penetrating beam.

- Precision machined aluminum reflector gives bright, narrow beam for sighting distant objects
- High impact ABS and polycarbonate case will not corrode, dent, conduct electricity or freeze to skin in cold weather
- Waterproof to 500 feet



Thumb or index finger activated rotary switch permits single hand operation

### Sunlight SL4

- Bright 5.5 watt, 112 lm beam powered by 4 alkaline C-cells
- Size: 6.2 x 2.46 x 1.7 inch

### Sunlight SL6

- Bright 8 watt, 201 lm beam powered by 6 alkaline C-cells
- Size: 8.7 x 2.46 x 1.7 inch

## UK 2L Lithium. Same beam and brightness as the UK4AA, but half the size

Powered by long shelf-life Lithium batteries. Great for use as a discrete high intensity light or for emergency illumination. Good for disaster kits.



- Two lithium batteries will last for 5 – 10 years of non-use
- Powerful 2.1 watt beam in a very small package (1.2 dia. x 4.4 inch)
- Extremely lightweight, water-resistant
- Clip included for attaching to gear
- Tough ABS, polycarbonate, PP rubber construction



Also Available As eLED



**Sunlight C4 & C8.  
Two great all  
weather lights**

Most versatile and feature packed 4 or 8 C-cell industrial light. Perfect for those who want big light features in a small package

**Sunlight C4**

- Bright 6 watt, 104 Lm Xenon beam powered by 4 alkaline C-cells
- Size: 3.2 dia x 5.2 inch

**Sunlight C8**

- Bright 13.2 watt, 245 Lm Xenon beam powered by 8 alkaline C-cells
- Size: 3.2 dia x 7 inch



Integral pistol grip and shock absorbing bezel cover

- Unique twin-lamp system allows for safety backup and 60 hours total lamp life
- Either of two high power Xenon lamps available with the flick of a switch
- Polarized battery compartment reduces battery leakage
- Tough, non-corroding ABS and polycarbonate plastic construction
- O-ring sealed against dust, water and mud
- Waterproof to 500 feet
- Rubber sleeve lanyard included

**UPGRADE C4/C8 To Rechargeable  
Get greater convenience and  
brightness or switch between  
alkaline & NiMH C-Cells**

See Page 7 For Details



Non-breakable  
Push Lock switch



**UK eLED  
Module Upgrade.  
Turn any UK C4/C8 light into the  
latest eLED technology**

See Technical Specifications On Page 15

**Sunlight D4 Vectra.  
A big light in a small package**

High intensity narrow beam light powered by 4 disposable D-cell batteries. Adjustable stainless steel floor stand and lantern-style grip included.

- Unique twin-lamp system allows for safety backup and 60 hours total lamp life
- Two 5.8 watt high power Xenon lamps available with the flick of a switch
- Polarized battery compartment reduces battery leakage
- Tough, non-corroding ABS and polycarbonate plastic construction
- Rubber sleeve lanyard included
- An adjustable lantern style carrying handle is also included
- Size: 4 dia. x 6 inch



Non-breakable  
locking switch

Adjustable base





## Drop it, Scrape it, Dunk it, Bang it,



### **UK All Environment Cases Provide Maximum Protection for Delicate Equipment**

Features you can depend on:

- Silicone o-ring sealed against water, corrosive gasses, sand and dust
- Passes one meter water submersion test
- Tough ultra high-impact grade ABS plastic construction which won't rust, dent or chip
- Padded free swinging plastic or spring return steel handles
- Plastic snap latches or stainless steel twist-lock latches
- Locking loops for padlocks or security seals
- Wheels and pull-out tote handle on Transit series cases
- Pressure equalization valve for easy opening after altitude or temperature change
- Optional diced foam filling or instrument panel mounting ring
- OEM custom markings, colors, interiors and product configurations

#### **Standards and Ratings:**

Designed to pass many of the tests outlined in MIL-STD 810F, MIL STD108 and MIL-T-28800 for water, dust, basic hot and cold and drop resistance.

UL-94 Flame Class Material Rating is HB (1/8 Inch). V-0 on special order.

Testable to IP68 ingress protection.

**GSA Contract Information Call 800 327-7388**



*Dry cases provide maximum protection for even the most sensitive equipment.*

# Splash it, Freeze it, Roll it, Count on it!

## Let UK protect and help you sell your OEM products. Modifications to meet your needs

Your OEM products will be well-protected and have greater sales appeal in UK Cases made from high-impact ABS plastic which is extremely tough and resists scratches, dents and corrosion. At the same time ABS is ideal for modifications which include drilling, solvent welding, conductive painting and other machining operations. Custom colors and materials are available in manufacturing quantities. Special custom foam cut-outs and densities can also be ordered.



*User configured closed cell dice foam filling is available with all cases. Sections of foam are easily removed to cradle delicate objects. Custom cut foam is also available.*

## Panel Rings. When your instruments require permanent installation

Instrument panel mounting flanges are available for the Dry Box and Dry Case series of products. Neoprene foam o-rings seal the panel to the flange and case preventing water and dust from damaging fragile components and circuits beneath the panel. Brass inserts (8-32 thread) are provided in the flange for attaching plastic and metal instrument panels.



*Panel mounting rings are available for Dry Boxes and Dry Cases. The ring is solvent welded in place 0.5 inch below the rim of the case. Brass threaded inserts (8-32) are embedded in the ring for rigid attachment of an instrument panel. A foamed neoprene O-ring seals the panel to the ring.*

## A Size for every Application.

### UK Dry Box Internal Dimensions (Inches)

Model	Length	Width	Depth	Lid Depth	Base Depth
<b>309</b>	8.5	6.0	3.0	.07	2.3
<b>409</b>	8.5	6.0	3.7	.07	3.0
<b>609</b>	8.5	6.0	5.7	.07	5.0

### UK Dry Case Internal Dimensions (Inches)

Model	Length	Width	Depth	Lid Depth	Base Depth
<b>613</b>	13.4	8.9	5.6	1.8	3.8
<b>716</b>	16.9	10.0	6.5	1.8	4.7
<b>518</b>	17.8	12.8	5.1	1.8	3.3
<b>718</b>	17.8	12.8	6.8	1.8	5.0
<b>821</b>	20.9	12.8	8.4	2.2	6.2

### UK Transit Case Internal Dimensions (Inches)

Model	Length	Width	Depth	Lid Depth	Base Depth
<b>822</b>	22.0	18.1	8.4	2.2	6.2
<b>1022</b>	22.0	18.1	10.9	4.7	6.2
<b>1122</b>	22.0	18.1	10.9	2.2	8.7
<b>1322</b>	22.0	18.1	13.4	4.7	8.7
<b>1422</b>	22.0	18.1	13.4	2.2	11.2
<b>1622</b>	22.0	18.1	15.9	4.7	11.2
<b>827</b>	27.0	18.1	8.4	2.2	6.2
<b>1027</b>	27.0	18.1	10.9	4.7	6.2
<b>1127</b>	27.0	18.1	10.9	2.2	8.7
<b>1327</b>	27.0	18.1	13.4	4.7	8.7
<b>1427</b>	27.0	18.1	13.4	2.2	11.2
<b>1627</b>	27.0	18.1	15.9	4.7	11.2





**Transit Cases.**  
**Maximum Protection For Large Equipment**

Large, but delicate objects can be transported in a UK Transit Case with maximum protection. Twelve sizes (see page 11) accommodate AV equipment, portable labs, test stations, specialized photographic gear, communication sets, etc. Choice of 2 or 4 inch lid depth makes the selection even more

versatile. Cases are available with or without the externally mounted heavy duty pull out handle and wheels. All cases include handles on both ends as well as the front for easy handling. Dual lock loops are provided for padlocks or security seals. Dice cut pluck-out foam filling is optional.

**Choose from 12 Sizes**







**613 Dry Case**  
13.4" x 8.9" x 5.6"



**716 Dry Case**  
16.9" x 10.0" x 6.5"



**518 Dry Case**  
17.8" x 12.8" x 5.1"



**718 Dry Case**  
17.8" x 12.8" x 6.8"



**821 Dry Case**  
20.9" x 12.8" x 8.4"

## Dry Cases. Water tight and extremely tough

Small enough for airline carry-on, tough enough for a storm. The o-ring sealed rigid shell of the UK Dry Case protects delicate contents from crushing, dust and water. Cases come standard with plastic snap latches, lock loop and padded folding handle. Optional twist-lock stainless steel latches and spring return handle meet military specifications. Instrument panel mounting flange, dice cut pluck-out foam and custom colors are also

available. These cases are ideal protection for instrumentation, sales presentation packages, test equipment, photographic equipment, guns and other delicate equipment.



## Dry Boxes. Protect your water sensitive items

Superior waterproof dry boxes for protecting water sensitive items. 309 box includes built-in handle while the 409 and 609 have detachable

nylon strap. Options include dice cut pluck-out foam, instrument panel mounting flange, transparent lid and custom colors.



**309 Dry Box**  
8.5" x 6.0" x 3.0"



**409 Dry Box**  
8.5" x 6.0" x 3.7"



**609 Dry Box**  
8.5" x 6.0" x 5.7"



# ACCESSORIES CUSTOMIZATION

## **SUPER HANGER.** **Extra strong, no rust**

This sturdy non-corroding hanger will hold heavy coats, turnouts, protective suits, etc. so that they can dry properly for the next use.

- One piece I-beam construction for strength
- Non-corroding plastic resin will not rust
- Supports up to 20 pounds
- Size: 1.2 x 16.6 x 9 inch

- 24001 Super Hanger - Yel
- 24002 Super Hanger - Blu
- 24003 Super Hanger - Blk



## **EXPOSURE SUIT HANGER.** **Heavy duty, thick shoulder**

This oversize hanger is made for holding heavy coats, hazmat suits, and other protective wear wide open for quick drying. Large radius shoulder prevent damage due to sharp corners.

- Strong enough to hang the heaviest water loaded gear
- Tall hook accommodates bulky collars
- Supports up to 50 pounds
- Non-corroding plastic resin and stainless coated hook will not rust
- 3.0 or 4.5 inch shoulder
- Size: 3.0 (4.5) x 15 x 16 inch



- 24041 Exposure Suit Hanger 3.0 inch - Blu
- 24051 Exposure Suit Hanger 4.5 inch - Blu

# C U S T O M I M P R I N T S

## **Brand Identification Program.** **Highlight your company name and logo or special event**

All UK lights can be imprinted with your company logo and information using 1 or 2 color pad printing techniques. Artwork should be supplied electronically as line art.



# SPECIFICATIONS

## RATINGS



	Color	Part #	Model	Switch	Lamp	Brightness	Battery	Charge Time	Burn Time	Certification	
	<b>UK4AA</b> Size: 6.1 x 1.5 x 1.2 inch										
	Yel	14107	AS2	Click	14801 Xenon	37.7 Lumen	Alkaline AA		4-5 Hr	C1D2	
	Blk	14108	AS2	Click	14801 Xenon	37.7 Lumen	Alkaline AA		4-5 Hr	C1D2	
	Orn	14109	AS2	Click	14801 Xenon	37.7 Lumen	Alkaline AA		4-5 Hr	C1D2	
	Yel	14110	AN2	Twist	14801 Xenon	37.7 Lumen	Alkaline AA		4-5 Hr	C1D2	
	Yel	14201	AS2R	Click	14824 Xenon	70.0 Lumen	NiMH AA	1.5 Hr	2.2 Hr	C1D2	
	Blk	14202	AS2R	Click	14824 Xenon	70.0 Lumen	NiMH AA	1.5 Hr	2.2 Hr	C1D2	
	Yel	14401	ASLED	Click	14830 eLED	15.0 Lumen	Alkaline AA		10-12 Hr	C1D2	
	Blk	14402	ASLED	Click	14830 eLED	15.0 Lumen	Alkaline AA		10-12 Hr	C1D2	
		<b>UK4AA eLED ZOOM</b> Size: 6.7 x 1.5 x 1.2 inch									
Yel		14501	AS2ZM	Click	14850 eLED	35.0 Lumen	Alkaline AA		4-10 Hr	C1D2	
Blk		14502	AS2ZM	Click	14850 eLED	35.0 Lumen	Alkaline AA		4-10 Hr	C1D2	
	<b>Unilite</b> Size: 6.7 x 2.5 x 1.4 inch										
	Yel	14161	AS2	Click	14801 Xenon	37.7 Lumen	Alkaline AA		4-5 Hr	C1D2	
	Blk	14162	AS2	Click	14801 Xenon	37.7 Lumen	Alkaline AA		4-5 Hr	C1D2	
	Orn	14163	AS2	Click	14801 Xenon	37.7 Lumen	Alkaline AA		4-5 Hr	C1D2	
	Yel	14414	ASLED	Click	14830 eLED	30.0 Lumen	Alkaline AA		10-12 Hr	C1D2	
	Blk	14415	ASLED	Click	14830 eLED	30.0 Lumen	Alkaline AA		10-12 Hr	C1D2	
	<b>UK2AA</b> Size: 4.2 x 1.5 x 1.1 inch										
	Yel	15001	AS2	Click	15801 Xenon	10.7 Lumen	Alkaline AA		4-5 Hr	C1D2	
	Blk	15002	AS2	Click	15801 Xenon	10.7 Lumen	Alkaline AA		4-5 Hr	C1D2	
	Orn	15003	AS2	Click	15801 Xenon	10.7 Lumen	Alkaline AA		4-5 Hr	C1D2	
	<b>UK2AAA Mini Pocket Light</b> Size: .74 x 2.9 x 1.1 inch										
	Yel	09005	MPL	Twist	09801 Xenon	10.7 Lumen	Alkaline AAA		2-2.5 Hr	C1D2	
	Blk	09007	MPL	Twist	09801 Xenon	10.7 Lumen	Alkaline AAA		2-2.5 Hr	C1D2	
	Yel	09101	MPLWLED	Twist	09805 W LED	2.0 Lumen	Alkaline AAA		20 Hr	C1D2	
	<b>UK2AAA Penlight</b> Size: .75 dia. x 4.8 inch										
	Yel	13005	PEN	Twist	09801 Xenon	10.7 Lumen	Alkaline AAA		2-2.5 Hr	C1D2	
	Blk	13007	PEN	Twist	09801 Xenon	10.7 Lumen	Alkaline AAA		2-2.5 Hr	C1D2	
	Yel	13101	PENWLED	Twist	09805 WLED	2.0 Lumen	Alkaline AAA		20 Hr	C1D2	
	<b>UK2AAA Penlight S</b> Size: .75 dia. x 5.1 inch										
	Yel	13201	PENS	Click	09801 Xenon	10.7 Lumen	Alkaline AAA		2-2.5 Hr	C1D2	
	Blk	13203	PENS	Click	09801 Xenon	10.7 Lumen	Alkaline AAA		2-2.5 Hr	C1D2	
	Yel	13301	PENSWLED	Click	09805 W LED	2.0 Lumen	Alkaline AAA		20 Hr	C1D2	
	<b>Sunlight SL4</b> Size: 6.2 x 2.46 x 1.7 inch										
	Yel	80009	SL4	Rotate	80501 Xenon	113 Lumen	Alkaline C		4-5 Hr	C1D2	
	Blk	80012	SL4	Rotate	80501 Xenon	113 Lumen	Alkaline C		4-5 Hr	C1D2	
	<b>Sunlight SL6</b> Size: 8.7 x 2.46 x 1.7 inch										
	Yel	18014	SL6	Rotate	18503 Xenon	201 Lumen	Alkaline C		4-5 Hr	C1D2	
	Blk	18017	SL6	Rotate	18504 Xenon	201 Lumen	Alkaline C		4-5 Hr	C1D2	
	<b>UK 2L Lithium</b> Size: 1.2 dia. x 4.4 inch										
	Yel	12005		Twist	14801 Xenon	37.7 Lumen	Lithium 123		3-4 Hr	C1D2	
	Blk	12007		Twist	14801 Xenon	37.7 Lumen	Lithium 123		3-4 Hr	C1D2	
	<b>UK 300</b> Size: 8.7 x 2.46 x 1.7 inch										
	Yel	22004		Twist	22806 Xenon	53 Lumen	Lithium 123		4-5 Hr	C1D2	
	Blk	22009		Twist	22806 Xenon	53 Lumen	Lithium 123		4-5 Hr	C1D2	
	Orn	22010		Twist	22806 Xenon	53 Lumen	Lithium 123		4-5 Hr	C1D2	
	<b>Sunlight C4</b> Size: 3.2 dia. x 5.2 inch										
	Yel	19011		Rotate	19904 Xenon	104 Lumen	Alkaline C		4-5 Hr	C1D2	
	Blk	19013		Rotate	19904 Xenon	104 Lumen	Alkaline C		4-5 Hr	C1D2	
	Yel	19041		Rotate	19928 eLED	130 Lumen	Alkaline C		6.5 Hr	C1D2	
	<b>Sunlight C8</b> Size: 3.2 dia. x 7 inch										
	Yel	19411		Rotate	19914 Xenon	245 Lumen	Alkaline C		4-5 Hr	C1D2	
	Blk	19413		Rotate	19914 Xenon	245 Lumen	Alkaline C		4-5 Hr	C1D2	
	Yel	19421		Rotate	19928 eLED	130 Lumen	Alkaline C		7.75 Hr	C1D2	
	<b>Sunlight D4 Vectra</b> Size: 4 dia. x 6 inch										
	Yel	44031		Rotate	44806 Xenon	104 Lumen	Alkaline D		7-10 Hr	C1D2	