

SL3—IN SOFT LIGHT LED STRIP — INDOOR

DESCRIPTION

Soft Light LED Strip 3 is a flexible 8mm linear LED strip. Available in lengths of 5m (16 ft.), it may be cut every 6 LEDs (50mm / 2"). It uses 120 LEDs per Meter (36 LEDs / ft)

FEATURES

- * 3M industrial strength adhesive tape (include)
- * Long life LED: 50,000 hours
- * Voltage Input: 24VDC
- * Dimmable with dimming power supply
- * 24" leads on both ends of each roll
- * CRI>91

SPECIFICATIONS

LAMP
LED: 10 watts/Meter (3 watts/ft)
LAMP LIFE
50,000 hours LM80
POWER INPUT
24 Volt DC power
CRI> 91
LUMENS
2700K = 788 lm/M (236 lm/ft)
3000K = 832 lm/M (249 lm/ft)
3400K = 876 lm/M (263 lm/ft)
4100K = 908 lm/M (279 Lm/ft)



Project: _____
 Type: _____
 Date: _____
 Part #: _____

ORDERING CODE	LENGTH	VOLTAGE	COLOR
SL3-IN	16	24V	2700
SL3-IN	16 ft	24 Volt	2700 K
			3000 K
			3400 K
			4100 K