

## PLATED CARRIAGE BOLTS BOULONS DE CARROSSE PLAQUÉS

**129**  
Series

Used extensively for Truck Rack and Floorboard construction or repair.  
Fully threaded for proper fit and adjustment in wood.

### ORDER BY STOCK NUMBER

Length Overall	Bolt Diameter							
	1/4	Std. Pkg.	5/16	Std. Pkg.	3/8	Std. Pkg.	1/2	Std. Pkg.
3/4	129-307	100	129-442	100	129-487	100	-	-
1	129-309	100	129-444	100	129-489	100	129-579	50
1-1/4	129-311	100	129-446	100	129-491	100	129-581	50
1-1/2	129-313	100	129-448	100	129-493	100	129-583	50
2	129-316	100	129-451	100	129-496	100	129-586	50
2-1/2	129-318	100	129-453	100	129-498	100	129-588	50
3	129-320	100	129-455	100	129-500	100	129-590	50
3-1/2	129-322	100	129-457	100	129-502	100	129-592	50
4	129-324	100	129-459	100	129-504	100	129-594	50
4-1/2	129-325	100	129-460	100	129-505	100	129-595	50
5	129-326	100	129-461	100	129-506	50	129-596	25
6	129-329	100	129-464	50	129-509	50	129-599	25
8	-	-	-	-	129-513	50	129-603	25
10	-	-	-	-	129-517	10	129-607	10
12	-	-	-	-	129-520	10	129-610	10



**Note:** Plated Grade 5 Carriage Bolts are available. See current price list Industrial Price Book. Full shank Carriage Bolts available upon request.

## PLATED CARRIAGE BOLTS BOULONS DE CARROSSE PLAQUÉS

**129**  
Series

### UTILITY ASSORTMENT

No. 020-330

- This Assortment contains 70 Plated Bolts and Nuts, 14 sizes.
- Each size in a compartment in a sturdy fibre-board container with retail prices shown.
- Particularly useful for farm, garage and general repair work.



## PLATED GRADE 5 PLOW BOLTS BOULONS DE CHARRUE CLASSE 5 PLAQUÉS

**133**  
Series

- Regular No. 3 Head
- High Carbon Steel
- Double Heat Treated

Papco® Plow Bolt heads are round and countersunk with a square neck. Oversize heads for 3/8" Dia. are 7/16" Dia. head and 7/16" Dia. is 1/2" Dia. head. Length is measured overall from end of bolt to the top of the head. Other heads and styles are available.

### ORDER BY STOCK NUMBER

Standard Package: 3/8" Dia. 100; 7/16" and 1/2" Dia. 50; 5/8" Dia. 25

Length Overall	Standard Head				Oversize Head		Length Overall	Standard Head				Oversize Head	
	3/8	7/16	1/2	5/8	3/8	7/16		3/8	7/16	1/2	5/8	3/8	7/16
1	133-489	133-534	-	-	-	-	2	133-496	133-541	133-586	133-675	-	133-820
1-1/4	133-491	133-536	133-581	-	133-791	-	2-1/4	-	-	-	133-676	-	133-822
1-1/2	133-493	133-538	133-583	133-672	133-793	-	2-1/2	133-498	133-543	133-588	133-677	-	133-824
1-3/4	133-495	133-540	133-585	133-674	-	133-816	3	-	133-545	133-590	133-679	-	-



## PLATED LAG BOLTS TIRE-FONDS PLAQUÉS

**135**  
Series

- Hex Head
- Sharp Gimlet Point

### ORDER BY STOCK NUMBER

Dia. Length	1/4	5/16	3/8	1/2	Dia. Length	1/4	5/16	3/8	1/2
1	135-309	135-444	-	-	4	135-324	135-459	135-504	135-594*
1-1/4	135-311	135-446	-	-	4-1/2	135-325	135-460	135-505	135-595*
1-1/2	135-313	135-448	135-493	-	5	135-326	135-461	135-506*	135-596*
2	135-316	135-451	135-496	135-586*	6	135-329	135-464	135-509*	135-599**
2-1/2	135-318	135-453	135-498	135-588*	7	-	-	135-511*	135-601**
3	135-320	135-455	135-500	135-590*	8	-	-	135-513*	135-603**
3-1/2	135-322	135-457	135-502	135-592*					



Standard Package: 100, \*50, \*\*25

Length of Lag Bolt is measured from under head to end of point. Thread is one-half of length plus 1/2". Larger and longer sizes are available.